

Heavy Duty Cutting Performance for Fencing...



Made Easier.



KNIPEX Quality – Made in Germany

Powerful. Tough. Exceptional.

Co-Bolt Fencing Cutter

For easy, exceptional cutting performance, the KNIPEX CoBolt Fencing Cutter is perfect for any job.



- precision-matched, induction hardened cutting edges are specially made to cut all types of fencing
- 20-to-1 compound joint ratio for exceptional cutting
- non-slip grip handles
- "R" = Robust. Designed to cut fence wire and barbed wire

Designed specifically for fencing.

71 01 200 R



Fencing

	Part #	UPC #	Description	med./hard	Capacity hard	piano wire	oz.
	71 01 200 R SBA	843221010201	8" Co-Bolt Fencing Cutter	13/64"	5/32"	–	11.8
	71 01 200 SBA	843221000257	8" CoBolt Mini Bolt Cutter	13/64"	5/32"	9/64"	11.8

New Orbis Fencing Cutter

Available with a Flat or Half Round Jaw

- for use in cutting, bending, and tying wire fencing
- flat and half round nose with 3 joint cutters
- long, slim head allows for greater reach
- polished head
- made of forged alloy tool steel
- ergonomically designed handles for better gripping and pulling
- additional gripping area underneath the joint for pulling

Available in 8" and 10" sizes.





90 51-200/2000



90 51-201/2000



Orbis is a division of the KNIPEX Group that specializes in the manufacturing and development of high-quality pliers. With over 75 years of experience, Orbis continues to focus on innovation and service and provides optimized logistics in more than 65 countries internationally.

	Part #	UPC #	Description	cuts med./hard	Capacity grips pipe	oz.
	90 51-200/2000	843221010522	8" Flat Nose Fencing Pliers	9/64"	1/2"	10.5
	90 51-250/2000	843221010546	10" Flat Nose Fencing Pliers	11/64"	3/4"	18
	90 51-201/2000	843221010539	8" Round Nose Fencing Pliers	9/64"	1/2"	12
	90 51-251/2000	843221010553	10" Round Nose Fencing Pliers	11/64"	3/4"	18



Superior Cutting – Less Effort.

High Leverage Diagonal Cutter



74 01 250

For heavy duty cutting with minimal effort and exceptional performance, only one tool will do – High Leverage Diagonal Cutting Pliers from KNIPEX.

- high leverage precision matched, induction hardened cutting edges cut soft, hard and ACSR wire
- heavy duty fixed forged axle rivet joint ensures smooth operation and long life
- non-slip grip handles



Available in 8" and 10" sizes.

	Part #	UPC #	Description	med./hard	Capacity hard	piano wire	oz.
	74 01 200 SBA	84322100264	8" High Leverage Diagonal Cutting Pliers	11/64"	1/8"	3/32"	9.3
	74 01 250 SBA	84322100271	10" High Leverage Diagonal Cutting Pliers	3/16"	9/64"	1/8"	13.8

High Leverage Center Cutter

74 91 250


Cuts hard so you don't have to.

- high leverage precision matched, induction hardened cutting edges cut soft, hard and ACSR wire
- features a high-impact center cutter
- heavy duty fixed forged axle ensures smooth operation and long life
- ergonomically designed handles



Heavy Duty

	Part #	UPC #	Description	med./hard	Capacity hard	piano wire	oz.
	74 91 250 SBA	843221001223	10" High Leverage Center Cutter	13/64"	5/32"	9/64"	13.9





More Power.

Wire Rope Cutter

Easily cuts wire rope and steel rods.

Key Features:

- induction hardened shear cutter cuts medium hard wire up to 6/25" in diameter
- two crimping profiles for end ferrules for wire rope
- features an opening spring and locking lever



95 61 190

	Part #	UPC #	Description	Copper / Aluminum Cable	Wire Rope	med. / hard	"hard	oz.
	95 61 190 SBA	84322100233	7 1/2" Wire Rope Cutter	9/32"	15/64"	5/32"	3/32"	11
	95 62 190 SBA	843221010171	7 1/2" Wire Rope Cutter w/ Comfort Grip handles	9/32"	15/64"	5/32"	3/32"	12.5

Cobra® High-Tech Water Pump Pliers

Size does matter.





Key Features:

- patented push-button adjustment maintains jaw size setting
- easily grips pipes, nuts, and bolts
- gripping surfaces with special hardened teeth are wear resistant and grip any shaped object
- self-locking on pipes and nuts means no slipping on the work piece



87 01 250



	Part #	UPC #	Description	Capacity mm ²	oz.
	87 01 250 SBA	843221000929	10" Cobra Water Pump Pliers	2"	10.6
	87 01 300 SBA	843221000936	12" Cobra Water Pump Pliers	2-3/4"	18.1
	87 01 400 SBA	843221000127	16" Cobra Water Pump Pliers	3-1/2"	42.5
	87 01 560	843221000240	22" Cobra Water Pump Pliers	4-1/2"	97.7



KNIPEX – Tools Designed with Your Hand in Mind.

KNIPEX-Tools is the Sales and Marketing Organization of KNIPEX-Werk and is located in Arlington Heights, Illinois. Founded in 1882, KNIPEX-Werk, Wuppertal, Germany is the largest manufacturer of professional quality pliers on earth. We concentrate our efforts on being the best pliers manufacturer in terms of quality, innovation, and efficiency and our pliers satisfy the highest expectations in terms of performance, ergonomics and service life. Our products are designed to meet the requirements of professional users, who must be able to rely on their tools in day-to-day work. With over one thousand separate styles and sizes, KNIPEX offers a complete range of pliers for almost every application in trade and industry.

KTLP EM 10 024



2035 S. Arlington Heights Rd.
Suite 110
Arlington Heights, IL 60005
847.398.8520
847.398.8526 (fax)
www.knipex-tools.com