



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



870SA 2-1/2 to 3 Alu FM7 Cover Stamped

Appleton/Oz Gedney

Catalog Number	870SA
Manufacturer	Appleton/Oz Gedney
Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 2-1/2 - 3 In, Form: 7, Mounting: Screw-In, Material: Stamped Aluminum, Finish: Natural Aluminum, Standard: UI 514A, UI 514B, UI File Number E2527, Csa C22.2 No. 18.3, Csa 065183, Nema FB-
Weight per unit	0.6600 (lbs/each)
Product Category	Alum

Features

Form	7
------	---

Material, Color, and Finish

Finish	Natural Aluminum
--------	------------------

Dimensions and Weight

Hub Size	2-1/2 - 3
----------	-----------

Descriptions

Description	2-1/2 TO 3 ALU FM7 COVER STAMPED
extra long description	APP 870SA 2 1/2-3 FM7 COVER STAMPED
Long Description	FM7 Wedge-Lok Blank Clip Cover With Screw, Hub Size: 2-1/2 - 3 IN, Form: 7, Mounting: Screw-In, Material: Stamped Aluminum, Finish: Natural Aluminum, Standard: UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-
Product Type	2 1/2-3 FM7 Cover Stamped-Alum
Special Features	Approved for use in wet locations;Stainless steel screws;The cover is secured with clips, not screws;Unique Wedge-Lok clip cover design allows easy removal without damaging the conduit body;Wiring capacity: 9.7 CU-IN as per NEC 314.16(A)

Manufacturer Information

Brand	Appleton
GTIN	00781381601238
Manufacturers Part Number	870SA
UPC	781381601238

Taxonomies, Classifications, and Categories

Category Description	FORM 7, 8, CONDULETS, COVERS, & GASKETS
Type	Blank Clip Cover With Screw

Packaging

Carton	1
Weight Per each	0.66



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	For FM7 Unilet Conduit Outlet Bodies
Mounting	Screw-In
standard	UL 514A, UL 514B, UL File Number E2527, CSA C22.2 No. 18.3, CSA 065183, NEMA FB-1