



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 8824GRTNK 8X8X24 N3R Wireway

Unity MFG

Catalog Number	8824GRTNK
Manufacturer	Unity MFG
Description	Slip-On Cover Trough, Slip On, Gray, Low Carbon Steel, 24 In Overall Length, 8 In Overall Height, 8 In Overall Width, Powder Coated, 15 LB
Weight per unit	15.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

### Features

Knockouts	NO
-----------	----

### Dimensions and Weight

Depth	8
Length	24
Width	8

### Descriptions

Description	8X8X24 N3R WIREWAY
extra long description	UNT 8824GRTNK N3R SCREW COVER GUTTE
Special Features	For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket

### Manufacturer Information

Brand	Unity
GTIN	00761515143094
UPC	761515143094

### Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	GRT Gutter Slip-On Cover Wiring Trough

### Packaging

Carton	1
Weight Per each	15

### Uses, Certifications, and Standards

Enclosure	NEMA 3R, IP32
standard	UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant