



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



891545 Omniconn RG-6 Quad F Compr Conn Black, 1, 000/Box

Ideal

| | |
|------------------|--|
| Catalog Number | 891545 |
| Manufacturer | Ideal |
| Description | Ideal, Compression Connector, Omniconn, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 Ohm, Ports Size: 7/16 In, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 In, Overall Jacket Diameter: 0.260 - 0.280 In |
| Weight per unit | 17.4 (lbs/each) |
| Product Category | Coaxial & Twinaxial Connectors |

Features

| | |
|----------|-------|
| Material | Brass |
|----------|-------|

Material, Color, and Finish

| | |
|--------|---------------|
| Finish | Nickel-Plated |
|--------|---------------|

Descriptions

| | |
|------------------------|---|
| Description | OMNICONN RG-6 QUAD F COMPR CONN BLACK, 1,000/BOX |
| extra long description | IDEAL 89-1545 RG6 QUAD CMPR,PLSTC,1 |
| Features | Connector Model: 6QFOCAccepts RG-6 Quad coax cablesCenter conductor range: AllDielectric diameter range: .175" - .183"Outer jacket diameter range: .270" - .295"Recommended cable prep/stripping tools: 45-605 PrepPRO; 45-526Recommended compression tools: 30-793 OmniSeal PRO XL; 33-632 Linear X3The IDEAL OmniConn F connector is a cable specific connector solution for RG-6 coax. The OmniConn connectors have a combination brass and plastic exterior and an inner O-ring to provide a weather proof connection suita |
| Long Description | IDEAL, Compression Connector, OmniCONN, F-Type, Material: Brass, Finish: Nickel-Plated, Nominal Impedance: 75 OHM, Ports Size: 7/16 IN, Coaxial Cable Type: RG-6, Bandwidth: 3 GHZ, Dielectric Diameter: 0.175 - 0.183 IN, Overall Jacket Diameter: 0.260 - 0.280 IN |
| Product Type | RG6 Quad CMPR, PLSTC, 1000 Bulk |
| Special Features | Features: Omniconn F Compression Connectors Install Easily Onto Standard RG 6 And RG 6Quad Cables; Non Corrosive Nickel Plated Brass Body And Polycarbonate Bushing; Delrin/Nylon Adapter Sleeve And O-Ring Provide Double Protection For A Watertight Seal; Free Spinning Hex Nut For Ease Of Installation Onto All 7/16 IN Ports 75 OHM Nominal Impedance; Bandwidth Up To 3 GHZ; Two-Piece Pre-Assembled Connectors; Nominal Impedance: 75 OHM; Ports Size: 7/16 IN; Coaxial Cable Type: RG-6; Bandwidth: 3 GHZ; Dielectric |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250681723 |
| Manufacturers Part Number | 89-1545 |
| UPC | 783250681723 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Datacom Wiring Devices and Accessories |
| Type | F-Type |

Availability

| | |
|-------------|------|
| minimum qty | 1000 |
|-------------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1000 |
| Weight Per each | 17.4 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Terminating an F Style connection onto RG 6 Quad Coax . |
|-------------|---|