



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-646-6192



## 89204 Terminal Strip, 4-Pole, 22-10 Awg

*Ideal*

Catalog Number	89204
Manufacturer	Ideal
Description	Terminal Strip, 4 Circuits, 4 Poles, 30 A, 600 V Ac, Steel (Screw) Material, -40 to +260 °F, 3.25 In Overall Length, 1.33 In Overall Width, 0.81 In Overall Height, 0.18 LB
Weight per unit	0.1800 (lbs/each)
Product Category	Power BLKS & Distribution BLKS

### Features

amperage rating	30
Spacing	0.562
Wire Size	22 - 10

### Descriptions

Description	TERMINAL STRIP, 4-POLE, 22-10 AWG
extra long description	IDEAL 89-204 TERMINAL STRIP 4-CIRCU
Special Features	Features: Torque Rating of 16 in-lbs; Rugged base eliminates breakage; Center spacing of 0.562 inch (14.3mm); Accepts up to #10 AWG wire; Corrosion resistant surface plates with #8 phillslot screws; Rated up to 600V, 30A; Accessory jumpers available; Heavy-duty, corrosion-resistant screws, surface plates and optional hardware; Accessory hardware provides a variety of termination options; Available cover helps prevent contact with live terminals; Rugged polyester thermoplastic base (UL Rated 94V-0); Operating

### Manufacturer Information

Brand	Ideal
GTIN	00783250892044
UPC	783250892044

### Taxonomies, Classifications, and Categories

Category Description	TERMINAL BLOCK ACCESSORIES
----------------------	----------------------------

### Packaging

Carton	1
Weight Per each	0.18

### Uses, Certifications, and Standards

standard	CSA, UL Listed, RoHS
----------	----------------------