



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



905BULK Scotchlok Electrical Idc, RD, 22-18awg *Minnesota Mining (3M)*

| | |
|------------------|---|
| Catalog Number | 905BULK |
| Manufacturer | Minnesota Mining (3M) |
| Description | 3M™ Scotchlok™ Insulation Displacement Connector 905 Is A Double Run or Tap Connector That Can Connect Two Wires In A Tap, Inline, Pigtail or Double Run Installation While Insulating The Connection. This Connector Is Ideal For Low Voltage Accessories and Electronics. |
| Weight per unit | 18.2 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Descriptions

| | |
|------------------------|---|
| Description | SCOTCHLOK ELECTRICAL IDC, RD, 22-18AWG |
| extra long description | 3M 7100175071 3M™ Scotchlok™ IDC C |
| Features | The connector insulation is manufactured from polypropylene and is rated for 32V applications. It withstands temperatures of 194 degrees F (90 degrees C). RoHS 2011/65/EU Compliant. |
| Long Description | 3M™ Scotchlok™ Insulation Displacement Connector 905 is a double run or tap connector that can connect two wires in a tap, inline, pigtail or double run installation while insulating the connection. This connector is ideal for low voltage accessories and electronics. |
| Product Type | 3M™ Scotchlok™ Idc Connector 905 |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Scotchlok |
| GTIN | 00054007061281 |
| Manufacturers Part Number | 905BULK |
| UPC | 054007061281 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | Insulation Displacement |

Availability

| | |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

Packaging

| | |
|-----------------|------|
| Carton | 5000 |
| Weight Per each | 18.2 |

Uses, Certifications, and Standards

| | |
|----------|----|
| standard | CE |
|----------|----|