



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



91100 Bilingual Caution Barricade Tape, 3" X 500', BK/YI

Brady Worldwide, Inc.

| | |
|------------------|--|
| Catalog Number | 91100 |
| Manufacturer | Brady Worldwide, Inc. |
| Description | Reinforced Barricade Tape Roll - Polyethylene, Caution, Black On Yellow, 3' X 500' |
| Weight per unit | 2.8 (lbs/each) |
| Product Category | Markers & Marking Tapes |

Features

| | |
|-------------|-------------------|
| Legend | CAUTION / CUIDADO |
| Material | Polyethylene |
| Roll Length | 500 |

Material, Color, and Finish

| | |
|--------|-----------------|
| Color | Black on Yellow |
| Finish | Gloss |

Dimensions and Weight

| | |
|-----------|-------|
| Thickness | 0.003 |
|-----------|-------|

Descriptions

| | |
|------------------------|--|
| Description | BILINGUAL CAUTION BARRICADE TAPE, 3" X 500', BK/YL |
| extra long description | BRADY 91100 REINFORCED BARRICADE TA |
| Features | Stronger than ordinary Barricade Tape, our Reinforced Tape is tough enough to be used again and again without stretching or sagging in sunlight or wind. |
| Long Description | Reinforced Barricade Tape Roll - Polyethylene, CAUTION, Black on Yellow, 3' x 500' |
| Product Type | Reinforced Barricade Tape |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Brady® |
| GTIN | 00754473911003 |
| Manufacturers Part Number | 91100 |
| UPC | 754473911003 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------|
| Category Description | TAPE |
| Type | Barricade Tape |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 2.8 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-----------------|
| Application | General Purpose |
| standard | OSHA 1910.144 |