ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685




# 9125 TAPE MEASURE, 25' SINGLE-HOOK

*KLEIN TOOLS*

| | |
|---|---|
| Catalog Number | 9125 |
| Manufacturer | KLEIN TOOLS |
| Description | Klein Tools Measuring Tapes deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade stands out to 13-Foot with a 16-Foot Reach. Able to endure the toughest of jobsite conditions, this tool also features a single hook, easy-to-read bold lines, and a retraction brake. |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Miscellaneous Hand Tools |

## Features

| | |
|---|---|
| Belt Clip | Yes |
| Material | Plastic Case with Steel Blade |
| Overall Height | 3.43" (8.7 cm) |
| Overall Width | 2.35" (6 cm) |
| Tape Length | 25' (7.6 m) |
| Graduations | 1/16'' |
| Media | Yes |

## Material, Color, and Finish

| | |
|---|---|
| Case Color | Black;Orange |
| Case Material | PC-ABS with TPR Overmolding |
| Tape Material | STEEL |

## Dimensions and Weight

| | |
|---|---|
| Overall Length | 3.43" (8.7 cm) |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

## Descriptions

| | |
|---|---|
| Description | TAPE MEASURE, 25' SINGLE-HOOK |
| Features | Klein Tools Measuring Tapes deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade stands out to 13-Foot with a 16-Foot Reach. Able to endure the toughest of jobsite conditions, this tool also features a single hook, easy-to-read bold lines, and a retraction brake. |
| Long Description | Klein Tools Measuring Tapes deliver performance and durability expected by professional tradespeople. Safeguarded by a thick and durable protective nylon-coating, the Tough Blade stands out to 13-Foot with a 16-Foot Reach. Able to endure the toughest of jobsite conditions, this tool also features a single hook, easy-to-read bold lines, and a retraction brake. |
| Product Type | 25 Foot Non-Magnetic Tape Measure |
| Special Features | 16-Foot Reach;Attachment Channel to Tether Tape Measure;Easy-to-read Bold Lines Every 1/8-Inch;Tough Blade |
| Extra Long Description | KLE 9125 25 Foot Non-Magnetic Tape |

## Manufacturer Information

| | |
|---|---|
| Brand | Klein Tools |
| GTIN | 00092644692673 |
| Manufacturers Part Number | 9125 |
| UPC | 783523 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | HAND TOOLS |
| Type | Closed Case, Double Sided Single Non-Magnetic Hook |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 6 |
| Weight | 20.7 |
| Weight Per Each | 1.3 (lbs/each) |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Linear Measurment |

# 13 FOOT STANDOUT

## WIDE, TOUGH, & DURABLE BLADE




Performance and durability expected by professional tradespeople

TOUGH BLADE

# 13 FOOT STANDOUT




**IMPACT RESISTANT HOUSING**
OVER-MOLDED WITH A SOFT TOUCH FINISH FOR EXCELLENT GRIP — STANDS UP TO JOBSITE DEMANDS

**HEAVY-DUTY, TOUGH, DURABLE NYLON-COATING**
PROTECTS BLADE PRINTING AND DELIVERS LONGER BLADE LIFE

**CONDUIT BENDING TABLE AND 3-PHASE LAYOUT GUIDE** PRINTED ON BACK-SIDE OF TAPE FOR CONVENIENCE


STRONG MAGNETIC DOUBLE-HOOK
ATTACHES TO CONDUIT AND STEEL STUDS. DOUBLE-HOOK ALLOWS FOR VIEWING THE MEASUREMENT SCALES PRINTED ON FRONT OR BACK OF TAPE
TETHER
CAPABLE
RETRACTION SPEED BRAKE CONTROLS BLADE SPEED AND PROTECTS FINGERS FROM TOUCHING BLADE
UNCLUTTERED, EASY-TO-READ BOLD LINES
MARKED ON BLADE EVERY 1/8-INCH

# PERFORMANCE AND DURABILITY EXPECTED BY PROFESSIONAL TRADESPEOPLE




| Cat. No. | UPC 0-92644+ | Blade Length | Hook | Magnetic | Measurement Scale | Tape Print |
|---|---|---|---|---|---|---|
| 9216 | 69266-6 | 16' (4.9m) | Double | Yes | Imperial | Double-sided |
| 9125 | 69267-3 | 25' (7.6m) | Single | No | Imperial | One-Sided |
| 9225 | 69269-7 | 25' (7.6m) | Double | Yes | Imperial | Double-sided |
| 9230 | 69272-7 | 30' (9.1m) | Double | Yes | Imperial | Double-sided |
| 9375 | 69271-0 | 7.5m (24.6') | Double | Yes | Metric and Imperial | Double-sided |

3 m

CE†

*Visit www.kleintools.com for safety warnings. Failure to follow all instructions and warnings may result in personal injury.
†CE applies to #9375 only.
US Patent D803711

## Tape Measure Holders


5195


5196


5195TT


5707



5712

| Holder Cat. No. | UPC 0-92644+ | Description | Fits Tape Measures |
|---|---|---|---|
| 5195 | 55078-2 | Medium Leather Pouch | 9216 |
| 5196 | 55092-8 | Large Leather Pouch | 9125, 9225, 9375, 9230 |
| 5195TT | 55537-4 | Tape Measure Holder With Ring | 9216 |
| 5707 | 55167-3 | Nylon Tape Measure Clip/Holder | 9216, 9125, 9225, 9375, 9230 |
| 5712 | 55131-4 | Nylon Pouch | 9216, 9125, 9225, 9375, 9230 |

KLEIN TOOLS®

See our complete line of **Levels & Measuring Tools**
**www.kleintools.com**

© 2019 Klein Tools, Inc.
Lincolnshire, IL 60069
82889 Rev. 08/19 A