



Square Junction Boxes	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	16.0	9339-Z+1	"Z" hanger, flush with face of plaster ring, wire clamps - bulk packed	1-¼	4-¼	4-¼	10314	50	22
	16.0	9339-Z+1C2	"Z" hanger, flush with face of plaster ring, 2 wire clamps - factory installed	1-¼	4-¼	4-¼	10318	50	23
	27.3	9342-C2	Bottom mount, 2 wire clamps - factory installed	2-¼	4	4	10346	50	25
	27.3	9342-HF	Nail-on "HF" hanger, wire clamps - bulk packed	2-¼	4	4	10348	50	30
	27.3	9342-HN	Nail-on "HN" hanger, wire clamps - bulk packed	2-¼	4	4	10342	50	32
	32.3	9343-N	Nails, Speed Klamps™ - bulk packed	2-½	4-1/16	4-1/16	10370	50	26
	32.3	9343-NC2	Nails, 2 wire clamps - factory installed	2-½	4-1/16	4-1/16	57150	50	27
	32.3	9343-NK	Nails, Speed Klamps™ - factory installed	2-½	4-1/16	4-1/16	10374	50	27
	32.3	9343-SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - bulk packed	2-½	4-1/16	4-1/16	10375	50	27
	32.3	9343-SSK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - factory installed	2-½	4-1/16	4-1/16	10376	50	27

Range/Dryer Receptacle	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	42.0	RD-42	Fetter ring nails, internal wire clamp - factory installed, knockout	3-13/16	4	3-¾	12907	24	22
	42.0	RD-42SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, internal wire clamp - factory installed, knockout	3-13/16	4	3-¾	12905	24	22

For use with 2-position devices; knockout accomodates #8 and #6 gauge wire.



Plaster Rings & Covers	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions			UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W	H			
	—	9315	Round blank cover	—	4-¾ dia.	—	10130	100	16
	—	9315-WH	Round blank cover, white	—	4-¾ dia.	—	10132	100	16
	—	9344	Square blank cover; *Use with series 9339, 9342, and 9343 only	—	4	4	10360	100	15
	4.2	9345	Single gang plaster ring, thermoplastic material, ½" offset	5/8	4	4	10361	100	8
	5.1	9345-58	Single gang plaster ring, thermoplastic material, 5/8" offset; *Use with series 9339, 9342, and 9343 only	¾	4	4	10372	50	5
	6.7	9346	Two-gang plaster ring, thermoplastic material, ½" offset	5/8	4	4	10362	50	4
	8.1	9346-58	Two-gang plaster ring, thermoplastic material, 5/8" offset; *Use with series 9339, 9342, and 9343 only	¾	4	4	10390	50	4
	4.8	9347	Square plaster ring, reduces to 3/0 outlet, ½" offset; *Use with series 9339, 9342, and 9343 only	11/16	4-1/16	4-1/16	10386	50	8
	4.3	9348	Round plaster ring, reduces 4" dia. outlet box to 3" dia. opening, ½" offset; *Use with series 9350, 9351, 9364 and 9365 only	5/8	4 dia.	—	10366	100	11

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.



Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9312-E	N/A	N/A	N/A	N/A	N/A	N/A
9312-EK	N/A	N/A	N/A	N/A	N/A	N/A
9312-EW	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9312-EWK	6062-402	4R-B	B225R	N/A	EZ25D0	N/A
9313-EW	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9313-EWK	6063-402	N/A	B355R	N/A	N/A	S3-52-W
9314-EWK	N/A	N/A	B468R	N/A	N/A	N/A
9315	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9315-WH	4062/WHITE	4R-B	E460R	N/A	EZYKL	N/A
9318	N/A	N/A	B112HB	N/A	N/A	N/A
9319	N/A	N/A	HB15W	N/A	N/A	N/A
9320	N/A	N/A	HB1DP	N/A	N/A	N/A
9322	N/A	N/A	HB1BL	N/A	N/A	N/A
9324-N	2070/N1614	N/A	N1614	N/A	N/A	N/A
9327-N	6090/7010/E1614	N/A	N/A	N/A	N/A	N/A
9329-EW	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9329-EWK	7010-8	232-OW	B225R	BH234R	N/A	S2-32-W
9331-E	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-EK	6090/7010	N/A	E1614	N/A	N/A	N/A
9331-ES	7010-8	N/A	N/A	N/A	N/A	N/A
9331-ESK	7010-8	N/A	N/A	N/A	N/A	N/A
9331-EW	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9331-EWK	6090-402	114-OW	B114R	N/A	EZ14S0	N/A
9335-16/16K	3190-C-94	N-321-C-94	N/A	N/A	N/A	N/A
9335-16G/16GK	N/A	N-321-GC-94	N/A	N/A	N/A	N/A
9335-BH/BHK	3190-C-94	N-321-C-95	N/A	N/A	N/A	S118HAC
9335-BHG/BHGK	N/A	N-321-GC-95	N/A	N/A	N/A	S118HGAC
9335-HNGK	N/A	N/A	N/A	N/A	N/A	N/A
9335-HNK	N/A	N/A	N/A	N/A	N/A	N/A
9335-N	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NG	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NGK	3190-40-PC	N/A	B518P	N/A	EZ18CNG	C118RGAC
9335-NK	3190/3190C	N/A	B518A/N-321-C	N/A	EZ18CN	C118RAC
9335-NKRED	N/A	3R-16-N-RED	N/A	N/A	EZ18CNAR	N/A
9336-16/16K	3090-94/3090-94-SQ	N/A	N/A	N/A	N/A	N/A
9336-16G/16GK	3090-94-40	N/A	N/A	N/A	N/A	N/A
9336-BH/BHK	3090-95/3090-95-SQ	3R-16-BH	N/A	N/A	N/A	N/A
9336-BHG/BHGK	3090-95-40	3R-16-BHGP	N/A	N/A	N/A	N/A
9336-HNGK	3090-N-40	N/A	N/A	N/A	N/A	N/A
9336-HNK	3090-N	N/A	N/A	N/A	N/A	N/A
9336-N	3190	3R16N	N/A	N/A	N/A	N/A
9336-NG	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NGK	3190-PC	3R16NGP	N/A	N/A	N/A	N/A
9336-NK	3190	3R16N	N/A	N/A	N/A	N/A
9338-E	3080	N/A	N/A	N/A	N/A	N/A
9338-EK	3080	N/A	N/A	N/A	N/A	N/A
9338-EKT	3080	N/A	N/A	N/A	N/A	N/A
9338-ES	3080-9/3080-9-PC	3R160W	N/A	BH614R	N/A	N/A
9338-ESG	3080-9-40	3R160WGP	B432A	BH614RP	N/A	N/A
9338-ESGK	3080-9-40	3R160WGP	B432A	BH614RP	N/A	C118WGAC