

# Levels

## Features:

**Top read level window** simplifies viewing in tight areas.

**Strong, die cast aluminum frame** features a convenient built-in hang hole.

**Handy V-grooved edge** for pipe and conduit work.

**Machined edges** for accurate readings.

**High impact acrylic vials** read plumb (vertical), level (horizontal), and 45°.

### Magnetic Torpedo Level



930-9

**Additional Features:**

- Magnetized strip on bottom.
- Yellow vials for easy viewing.

Cat. No.	Overall Length	Weight (lbs.)
930-9	9" (229 mm)	.36

### Rare Earth Magnet Torpedo Level



931-9RE

**Additional Features:**

- Powerful Rare Earth magnets hold firmly to iron and steel surfaces.
- Rare Earth magnets are up to five times stronger than strip magnets.
- Yellow vials framed with E-Z SEE® glow-in-the-dark material for easier viewing in dimly lit areas.

Cat. No.	Overall Length	Weight (lbs.)
931-9RE	9" (229 mm)	.36

### 6" Electrician's Level

**NEW!**



931-6RE

- Large, high visibility vials are easy to read.
- Unique 3 point design holds securely to pipe.
- Strong Rare Earth magnets firmly hold the level to ferrous metals.
- For use in measuring bends in conduit.
- Machined billet aluminum design.
- High contrast laser etched markings for high visibility readings.

Cat. No.	Overall Length	Weight (lbs.)
931-6RE	6" (152 mm)	1.00

### 9" Torpedo Level

**NEW!**



932-9RE

- Large high visibility vials are easy to read.
- Strong Rare Earth magnets firmly hold the level to ferrous metals.
- Easy to read vials set for measurements at 0, 30, 45 and 90 degrees.
- Machined billet aluminum design.
- High contrast laser etched markings.

Cat. No.	Overall Length	Weight (lbs.)
932-9RE	9" (229 mm)	1.00

All dimensions are in inches and (millimeters) unless otherwise specified.

**⚠WARNING:** Always wear approved eye protection.

