

fiberglass BOX™ 4" Dia. Round Outlet

Wall or Ceiling Fixture Support Boxes



NOTE: All 4" round outlet boxes have combination fixture mounting patterns (at widths of 2.75" and 3.5") with machine tapped holes to accept #8-32 mounting hardware.

HF, HL, & HN Hangers	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	22.5	9350-HFK	"HF" hanger, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	10419	50	28
	22.5	9350-HL	"HL" hanger, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	10424	50	27
	22.5	9350-HLC2	"HL" hanger, 2 wire clamps - factory installed	2-7/16	4	50 lb.	10425	50	29
	22.5	9350-HLK	"HL" hanger, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	62094	50	27
	22.5	9350-HLGK	"HL" hanger, ground strap, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	10443	50	27
	22.5	9350-HN	"HN" hanger, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	10460	50	30
	22.5	9350-HNK	"HN" hanger, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	10462	50	31



Adjustable Bar Hanger for 16" to 24" O.C. Joist Applications	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	15.0	9364-BH	16" - 24" adjustable bar hanger, Speed Klamps™ - bulk packed	1-11/16	4	50 lb.	88112	24	30
	15.0	9364-BHC2	16" - 24" adjustable bar hanger, 2 wire clamps - factory installed	1-11/16	4	50 lb.	88122	24	30
	15.0	9364-BHK	16" - 24" adj. bar hanger, Speed Klamps™ - factory installed	1-11/16	4	50 lb.	88113	24	30
	15.0	9364-BHG	16" - 24" adj. bar hanger, ground strap, Speed Klamps™ - bulk packed	1-11/16	4	50 lb.	88114	24	30
	15.0	9364-BHGC2	16" - 24" adjustable bar hanger, ground strap, 2 wire clamps - factory installed	1-11/16	4	50 lb.	88123	24	31
	15.0	9364-BHGK	16" - 24" adjustable bar hanger, ground strap, Speed Klamps™ - factory installed	1-11/16	4	50 lb.	88115	24	30
	22.5	9350-BH	16" - 24" adjustable bar hanger, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	88108	24	32
	22.5	9350-BHC2	16" - 24" adjustable bar hanger, 2 wire clamps - factory installed	2-7/16	4	50 lb.	88120	24	33
	22.5	9350-BHK	16" - 24" adj. bar hanger, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	88109	24	32
	22.5	9350-BHG	16" - 24" adjustable bar hanger, ground strap, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	88110	24	32
	22.5	9350-BHGC2	16" - 24" adjustable bar hanger, ground strap, 2 wire clamps - factory installed	2-7/16	4	50 lb.	88121	24	33
	22.5	9350-BHGK	16" - 24" adjustable bar hanger, ground strap, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	88111	24	32

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

