





fiberglass BOX™ 4" Dia. Round Outlet

Wall or Ceiling Fixture Support Boxes



NOTE: All 4" round outlet boxes have combination fixture mounting patterns (at widths of 2.75" and 3.5") with machine tapped holes to accept #8-32 mounting hardware.

Bottom Mount	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	15.0	9364	 Bottom mount, Speed Klamps™ - bulk packed	1-11/16	4	50 lb.	15080	50	25
	15.0	9364-K	 Bottom mount, Speed Klamps™ - factory installed	1-11/16	4	50 lb.	10622	50	25
	22.5	9350	 Bottom mount, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	10420	50	21
	22.5	9350-K	 Bottom mount, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	10418	50	21

Nail-On	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	15.0	9365-N	Fetter ring nails, Speed Klamps™ - bulk packed	1-11/16	4	50 lb.	10630	50	21
	15.0	9365-NK	Fetter ring nails, Speed Klamps™ - factory installed	1-11/16	4	50 lb.	75391	50	22
	22.5	9351-N	Fetter ring nails, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	10475	48	25
	22.5	9351-NC2	Fetter ring nails, 2 wire clamps - factory installed	2-7/16	4	50 lb.	65190	48	26
	22.5	9351-NK	Fetter ring nails, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	10476	48	25
	22.5	9351-NKRED	Fetter ring nails, Speed Klamps™ - factory installed *Molded in red for fire circuits	2-7/16	4	50 lb.	96502	25	13
	22.5	9351-NG	Fetter ring nails, ground strap, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	65210	48	24
	22.5	9351-NGC2	Fetter ring nails, ground strap, 2 wire clamps - factory installed	2-7/16	4	50 lb.	65220	48	26
	22.5	9351-NGK	Fetter ring nails, ground strap, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	65212	48	26



Steel Stud Screws	Cu. In. Volume	Catalog Number	Component Description	Exterior Dimensions		Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Wt. (lb.)
				D	W				
	22.5	9351-SS	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - bulk packed	2-7/16	4	50 lb.	65991	48	24
	22.5	9351-SSK	Steel stud screws for use with non-load-bearing studs 22 gauge or lighter, Speed Klamps™ - factory installed	2-7/16	4	50 lb.	65992	48	24

All dimensions are in inches unless otherwise noted.
See page 7 for Attachment Coding suffix descriptions.

Competitive Cross Reference

Fiberglass Outlet Boxes



ALLIED
MOULDED
PRODUCTS, Inc.

fiberglassBOX™: Premium Series “Hard Box” Fiberglass Boxes continued

Allied Moulded	Carlton® PH (Union Phenolic)	Carlton® PC Black Polycarbonate	Carlton® PVC (Zip Blue)	Carlton® PVC (SuperBlue®)	Cantex® (EZ BOX®)	Pass & Seymour (Slater®)
9338-ESGKT	3080-9-40	N/A	N/A	N/A	N/A	C118WGAC
9338-ESK	3080-9/3080-9-PC	3R160W	N/A	BH614R	N/A	N/A
9338-ESKT	3080-9-PC	N/A	N/A	N/A	N/A	N/A
9338-EST	3080-9-PC	N/A	N/A	N/A	N/A	N/A
9339-Z+1	4020-1-02	N/A	4S-812C	N/A	EZ18XN	N/A
9342-HF	N/A	N/A	N/A	N/A	N/A	N/A
9342-HN	N/A	N/A	N/A	N/A	N/A	N/A
9343-N	4000-02	4S32N	B432A	N/A	EZ32XN	S4435RAC
9343-NK	4000-02	4S32N	B432A	N/A	EZ32XN	S4435RAC
9343-SS	4000-02	N/A	N/A	N/A	N/A	N/A
9343-SSK	4000-02	N/A	N/A	N/A	N/A	N/A
9344	4041	4SB	A400/4SPB	N/A	EZXL	N/A
9345	4042-12	4S1G	A410	N/A	EZ03SXA	RC1
9345-58	N/A	N/A	A411	N/A	EZ04ES	N/A
9346	4022-12	4S2G	A420	N/A	EZ06DXA	RC2
9346-58	N/A	N/A	A421	N/A	EZ08ED	N/A
9347	4043-12	N/A	N/A	N/A	N/A	N/A
9348	4061	N/A	A471	N/A	EZ03YC	N/A
9350-16/16K	4070-94/4070-9402	N-423-C-94-V	N/A	BH525H	N/A	N/A
9350-16G/16GK	N/A	N-423-GC-94-V	N/A	BH525HP	N/A	N/A
9350-BH/BHK	4070-95/4070-9502/4070-95-PC	N-423-C-95-V	N/A	N/A	EZ20CH	S120HAC
9350-BHG/BHGK	4070-95-40	N-423-GC-95-V	N/A	N/A	EZ20CHG	S120HGAC
9350-HFK	N/A	N/A	N/A	N/A	N/A	S120JAC
9350-HL	4070-302	N/A	B620L	N/A	N/A	S120JAC
9350-HLGK	N/A	N/A	N/A	N/A	N/A	S120JGAC
9350-HLK	4070-302	N/A	B620L	N/A	N/A	S120JAC
9350-HN	4070-NO2	N/A	N/A	N/A	N/A	S120JAC
9350-HNK	4070-NO2	N/A	N/A	N/A	N/A	S120JAC
9350-K	N/A	N/A	N/A	N/A	N/A	N/A
9350	N/A	N/A	N/A	N/A	N/A	N/A
9351-N	4170/4170PC	4R20N	B520A/N-423-C	BH525A	EZ20CN	S120RAC
9351-NG	4070-N-40	4R20NGP	B520P/N-423-GC	BH525P	EZ20CNG	S120RGAC
9351-NGK	4070-N-40	4R20NGP	B520P/N-423-GC	BH525P	EZ20CNG	S120RGAC
9351-NK	4170/4170PC	4R20N	B520A/N-423-C	BH525A	EZ20CN	S120RAC
9351-NKRED	N/A	N/A	N/A	N/A	EZ20CNAR	N/A
9351-SS	4070-N-S	N/A	N/A	N/A	N/A	N/A
9351-SSK	4070-N-S	N/A	B618R	BH525S	N/A	N/A
9355-G	3000-02-40	N/A	N/A	N/A	N/A	C118WGAC
9355-GK	3000-02-40	N/A	N/A	N/A	N/A	C118WGAC
9355-K	3000	N/A	N/A	N/A	N/A	C118WAC
9355-S	3000-902-40	N/A	B618R	N/A	EZ18C0	C118WAC
9355-SGK	3000-902-40	N/A	B618R	N/A	EZ19C0G	C118WAC
9355-SK	3000-902-40	N/A	B618R	N/A	EZ18C0	C118WAC
9355	3000	N/A	N/A	N/A	N/A	C118WAC
9361-E	N/A	N/A	N/A	N/A	N/A	N/A
9361-EK	N/A	N/A	N/A	N/A	N/A	N/A
9361-ES	N/A	N/A	N/A	N/A	N/A	N/A