## **Dimmers & Fan Speed Controls**

Today's home and business owners want optimum control of their electrical systems. P&S Dimmers & Fan Speed Controls provide that control — along with aesthetics, durability, trouble-free installation, and innovative technologies.

#### Benefits of Using Legrand/Pass & Seymour Dimming

**Save Energy** – Dimming reduces the amount of energy consumed by the lamps which reduces energy costs.

Add ambience - Change the lighting to set the mood or highlight the décor.

Add comfort - Use only the light you need for the task.

**Add flexibility** – Change the look of the room and then change it back. Quickly and easily.

**Add convenience** – Presets and scene controls make it easy to set up your home the way you like with accuracy and repeatability.

Increase safety and security - Never drive up to a dark house again.

**Lower maintenance costs** – Dimming increases the life of incandescent lamps.

Add value - A home with lighting controls is worth more.







# Index

Device	Page Number	
Product Selection Guide	M-2	
Catalog Numbering System	M-3	
Residential Dimmers & Fan Speed Controls		
RF Lighting Control System	M-4 – M-7	
Scene Director	M-8, M-9, M-34	
Leandro®	M-10, M-34	
Harmony™ TradeMaster®	M-11, M-12, M-34	
TradeMaster® Toggle	M-18, M-19, M-20, M-36	
Rotary R TradeMaster® Series	M-21	
Residential & Light Commercial Dimmers & Fan Speed Controls		
LS TradeMaster® Series	M-13 – M-15, M-35	
DR TradeMaster® Series	M-16, M-34	
Wide Slide TradeMaster® Series	M-17, M-36	
Rotary TradeMaster® Series	M-22, M-23, M-37	
Commercial Dimmers & Fan Speed Controls		
Titan™ Series	M-24 – M-31, M-38	
Rotary Dimmers	M-32	
Rotary Fan Speed Controls	M-33, M-39	

# Pass & Seymour

**Dimmers & Fan Speed Controls** 

## **Dimmers & Fan Speed Controls Product Selection Guide**





**D**legrand

Energy concerns have created directives in some states for lighting controls in new residential construction and major renovations. In an effort to reduce electrical power consumption, California has mandated one of the most stringent energy codes in the country. California Title 24 requires high efficacy luminaires, vacancy sensors (Section L), or dimmers to be placed in certain areas of the home. The standard became effective on October 1, 2005. Other states are considering adopting similar mandates to answer their own energy concerns. Legrand/Pass & Seymour has an extensive selection of vacancy sensor and dimmer solutions to address this growing industry trend.



### **RF Lighting Control System**

- Whole house and room scene controls allow homeowners to change their environment at the push of a
- Frequency-agile Radio Frequency (RF) wireless communications
- Simple, intuitive programming without the use of a computer or controller. PAGES M-4 - M-7
- Leandro<sup>®</sup> Decorator Dimmers
- Multi-location dimming.
- Light levels fade elegantly up/down.
- Green LEDs indicate preset level; red LED makes dimmers easy to find in the dark.

dimmers easy to find at night.

Convenient preset dimming control.

separate preset for dimming control.

Combines ON/OFF toggle with

Matches appearance of toggle

Match appearance of toggle

No loss of settings during power

Illuminated versions available.

**PAGES M-13 - M-15** 

**PAGE M-18, M-19** 

PAGE M-20

Available in both preset and non-preset models.

**Toggle Dimmers** 


switches.

switches.

outages.

**PAGE M-10** 





- Select any lighting scene at the touch of a button.
- Optional infrared remote enables control from anywhere in the room.
- Master can control up to 30 dimmers.
- Easy to program and won't lose programming during power outage.

#### PAGES M-8, M-9

#### Harmony<sup>™</sup> Decorator Dimmers

- Matches P&S Decorator devices.
- Combines ON/OFF Decorator switch with separate slider for dimming control.
- No lost settings during power outages.

#### PAGE M-11, M-12

#### **DR Series Decorator Rotary** Dimmers

- Illuminated knob shows light level.
- Snap-in LED light modules make dimmers easy to find at night.
- Available for incandescent and low-voltage lighting.

#### **PAGE M-16**

#### **Rotary Dimmers**

- Models for incandescent and low-voltage lights; preset and illuminated features available.
- Simple to operate.
- Available in both preset and non-preset models.

PAGE M-21






## Dimmers & Fan Speed Controls Catalog Numbering System

Pass & Seymour

**D**legrand





Many P&S Dimmers & Fan Speed Controls are available boxed or VisionPak<sup>™</sup> clam-shell packaging for high-impact merchandising. Please see the Catalog Numbering System above or specific charts for ordering information.



## Residential Dimmers & Fan Speed Controls Rotary TradeMaster<sup>®</sup> Fan Speed Controls

#### **No-Noise De-Hummers**

Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3 or 4-speed levels in slide, rotary and dual styles with virtually no fan motor noise.

Catalog Number	Description	Ratings	Color
1.5A Max. Specification Grade Rotary Fan Speed Controls – No-Noise De-Hummers, RFI Protected*			
94003I 94003W	3-Speed, Low-Medium-High	120V 1.5A max.	lvory White
94004CL 94004I 94004W 94004LA	4-Speed, Low-High	120V 1.5A max.	Clear Ivory White Light Almond

\* Available in VisionPak<sup>™</sup> packaging, add "V" to Catalog Number. Example: 94003LAV.

Dual Control Features	
<ul><li>Fits one gang box.</li><li>Controls both fan speed and light level.</li></ul>	Decorator styling.

Catalog Number	Description	Ratings	Color
1.5A/300W Max. Specification Grade Dual Controls – No-Noise De-Hummers*			
94315I 94315W 94315LA	3-Speed Fan Control and 2-Level Hi/Low Dimmer	120V 1.5A/300W max.	lvory White Light Almond
94215I 94215W 94215LA	4-Speed Fan Control and 2-Level Hi/Low Dimmer	120V 1.5A/300W max.	Ivory White Light Almond

Requires 3 wire installation.


\* Available in VisionPak™ packaging, add "V" to Catalog Number. Example: 94315LAV.


Catalog Number	Description	Ratings	Color
3A/300W Max. Specification Grade Dual Controls*			
943311	Dial Speed Control and Dimmer	120V	lvory

\* Available in VisionPak<sup>™</sup> packaging, add "V" to Catalog Number. Example: 94331IV.


Catalog Number	Description	Color
Accessories for Dual Controls		
109019V 109020V 109018V	Adapter Kit for Dual Fan/Light Controls	lvory White Light Almond

Note: All controls on this page may be ganged without de-rating.





**Dimmers & Fan Speed Controls** 






## Devices & Wall Plates Color Selection Chart



Pass & Seymour

**Devices & Wall Plates** 



To order custom metal wall plates, see Pages Q-43 – Q-45.

For additional colors consult factory.