

# Soundsational™ Speaker Cable



94722

## Pro Audio Cable (high-strand, pressure-extruded, round)

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94762	16/2 stranded BC (65/34) 99.97% OFC	16	2	CL3	31 lbs	0.192"	500' Box (45)	White (01) Yellow (02)
94764	16/4 stranded BC (65/34) 99.97% OFC	16	4	CL3	47 lbs	0.224"	500' Box (45)	Blue (06)
94742	14/2 stranded BC (105/34) 99.97% OFC	14	2	CL3	44 lbs	0.222"	500' Box (45)	White (01) Yellow (02)
94744	14/4 stranded BC (105/34) 99.97% OFC	14	4	CL3	69 lbs	0.260"	500' Box (45)	
94722	12/2 stranded BC (168/34) 99.97% OFC	12	2	CL3	73 lbs	0.278"	500' Reel (05)	White (01) Purple (13)



94542 94564

## Complete Audio Cables (direct burial, high-strand, tubed construction)

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94562	16/2 stranded BC (65/34) 99.97% OFC	16	2	CL3	24 lbs	0.188"	1000' Box (46)	White (01) Blue (06)
94564	16/4 stranded BC (65/34) 99.97% OFC	16	4	CL3	43 lbs	0.220"	500' Box (45)	
94542	14/2 stranded BC (105/34) 99.97% OFC	14	2	CL3	35 lbs	0.218"	1000' Box (46)	White (01) Yellow (02)
94544	14/4 stranded BC (105/34) 99.97% OFC	14	4	CL3	64 lbs	0.256"	1000' Box (46)	



94642 94664

## Easy Audio Cables (direct burial, tubed construction)

Part Number	Description	AWG	Cond	UL Type	Weight (Nom.)	Outside Dia. (Nom.)	Packaging	Jacket Color
94662	16/2 stranded BC (26/30) 99.97% OFC	16	2	CL3	23 lbs	0.188"	500' Box (45)	White (01) Blue (06)
94664	16/4 stranded BC (26/30) 99.97% OFC	16	4	CL3	42 lbs	0.220"	500' Box (45)	
94642	14/2 stranded BC (41/30) 99.97% OFC	14	2	CL3	34 lbs	0.218"	500' Box (45)	White (01) Yellow (02)
94644	14/4 stranded BC (41/30) 99.97% OFC	14	4	CL3	63 lbs	0.256"	500' Box (45)	

