



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



97030I Wall Box Decorator Rotary Timer, Ivory

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 97030I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Wall Box Decorator Rotary Timer, 30 Min, 1HP, 20A 125V, 10A 250-277V, No Hold |
| Weight per unit | 0.3575 (lbs/each) |
| Product Category | Electromechanical Time Switches |

Features

| | |
|-----------------|--------------------|
| action | Single pole |
| amperage rating | 10/20 |
| Coil Voltage | 120VAC @ 60Hz |
| connection | Back and side wire |
| media | Yes |
| Timing Range | 30 minutes |
| Voltage Rating | 125, 250/277 |

Material, Color, and Finish

| | |
|-------|-------|
| Color | Ivory |
|-------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | 1.85" Depth x 1.8" Width x 4.2" Height |
|------|--|

Descriptions

| | |
|------------------------|---|
| Description | WALL BOX DECORATOR ROTARY TIMER, IVORY |
| extra long description | P&S 97030I DISC NO SUB |
| Long Description | Wall Box Decorator Rotary Timer, 30 min, 1hp, 20A 125V, 10A 250-277V, No Hold |
| Product Type | Disc No Sub |
| Special Features | Wall Box Rotary Timer |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007970302 |
| Manufacturers Part Number | 97030I |
| UPC | 785007970302 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------|
| Category Description | TIMERS |
| Type | 30 Minute Timer |

Trade Size

| | |
|----------|------|
| Amperage | 10.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 12 |
| Weight Per each | 0.3575 |

Uses, Certifications, and Standards

| | |
|-----------------------|--|
| Application | Residential |
| Mounting | BOX |
| Operating Temperature | Between 0°C and 40°C |
| standard | UL, CSA, CULUS, CSA Listed, cULus, UL Listed |