



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A16H1208SSLP 16X12X8 N4X SS4 CH Clamp CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A16H1208SSLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 16X12X8, Brushed, SS304
Weight per unit	23.6 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

### Features

ip rating	IP66
Material	Stainless Steel 304

### Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

### Dimensions and Weight

Depth	8
Height	16
Size	16.00x12.00x8.00 in
Width	12

### Descriptions

Description	16X12X8 N4X SS4 CH CLAMP CVR
extra long description	NVENT HOF A16H1208SSLP Stainless En
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 16x12x8, Brushed, SS304
Product Type	Stainless Encl. 16.00X12.00X8.

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510240202
Manufacturers Part Number	A16H1208SSLP
UPC	783510240202

### Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	23.6

## Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X Watertight, corrosion-resistant