

Eaton A200M2CAC

Catalog Number: A200M2CAC

Eaton Freedom NEMA motor control starter, Non-reversing starter, 120 VAC coil voltage, 45A, Three-pole, Size 2, 7-1/2 hp at 115V, 10 hp at 208V, 15 hp at 240V, 25 hp at 480,600V, A200 series, Wired for Separate Control



General specifications

Product Name	Catalog Number
Eaton A200 NEMA motor control	A200M2CAC
UPC	Product Length/Depth
786678231211	8.2 in
Product Height	Product Width
5 in	6.1 in
Product Weight	Certifications
4.2 lb	UL Listed CSA Certified

Catalog Notes

For ambient compensated overload relay with auto-reset, add Suffix D.

defaultTaxonomyAttributeLabel

Resources

Accessories

Motor control

Coil voltage

120 VAC

Catalogs

Eaton's Volume 5—Motor Control and Protection

Installation instructions

Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

Specifications and datasheets

Eaton Specification Sheet - A200M2CAC



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia