



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636



A200M3CADC SZ3 90A 3P Non Rev Starter Freedom Series

Eaton Corp

Catalog Number	A200M3CADC
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, Non-Reversing Starter, Three-Pole, Size 3, 25 HP At 208V, 30 HP At 240V, 50 HP At 480, 600V, A200 Series, Wired For Separate Control, 90A, 120V/60 HZ or 110V/50 HZ Coil Voltage
Weight per unit	115.0 (lbs/each)
Product Category	Nema Non-Combination Starters

Dimensions and Weight

Depth	6.75
Height	9.94
Width	4.63

Descriptions

Description	SZ3 90A 3P NON REV STARTER FREEDOM SERIES
extra long description	ETN A200M3CADC A200 M3CADC
Features	All Class A200 non-reversing starters utilize Type B three-pole overload relays with optional Type A for auto reset applications. Sizes 5 and 6 include the needed current transformers. Moving and stationary contacts are front accessible for simple and easy inspection and maintenance. All Class A200 starters are UL listed and recognized and are CSA certified.
Long Description	Eaton Freedom NEMA motor control starter, Non-Reversing Starter, Three-pole, Size 3, 25 hp at 208V, 30 hp at 240V, 50 hp at 480,600V, A200 series, Wired for Separate Control, 90A, 120V/60 Hz or 110V/50 Hz coil voltage
Product Type	A200 M3cadc

Manufacturer Information

Brand	Eaton Corp
GTIN	00786678232508
Manufacturers Part Number	A200M3CADC
UPC	786678232508

Taxonomies, Classifications, and Categories

Category Description	FREEDOM/NEMA STYLE
----------------------	--------------------

Packaging

Carton	1
Weight Per each	115



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636

Uses, Certifications, and Standards

Application

Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard

CSA Certified,UL Listed