



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1755 Enterprise Street
75751-0000, TX Athens
Phone: 903-675-7999
Fax: 903-675-9414



A201608LP 20X16X8 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A201608LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 20X16X8, Gray, Mild Steel
Weight per unit	27.5 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

ip rating	IP66
Material	Steel

Material, Color, and Finish

Finish	Powder Coated
--------	---------------

Dimensions and Weight

Depth	8
Height	20
Size	20.00x16.00x8.00 in
Width	16

Descriptions

Description	20X16X8 N12 CH CLMP CVR
extra long description	NVENT HOF A201608LP Enclosure 20.00
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 20x16x8, Gray, Mild Steel
Product Type	Enclosure 20.00X16.00X8.00
Short Description	Enclosure 20.00x16.00x8.00

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510281601
Manufacturers Part Number	A201608LP
UPC	783510281601

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	27.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1755 Enterprise Street
75751-0000, TX Athens
Phone: 903-675-7999
Fax: 903-675-9414

Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12