



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A242412LP 24X24X12 N12 CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A242412LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wall-Mount Enclosure, Steel, Type 12 Continuous Hinge, Wall Mount, White (Inside);Ansi 61 Gray (Outside), White (Inside);Gray (Door), 24 In Overall Width, 24 In Overall Length, 12 In Overall Height, 58 LB
Weight per unit	58.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Material, Color, and Finish

Finish	Powder Coated
--------	---------------

### Dimensions and Weight

Depth	12
Height	24
Size	24.00x24.00x12.00 in
Width	24

### Descriptions

Description	24X24X12 N12 CH CLMP CVR
extra long description	NVENT HOF A242412LP Enclosure 24.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510285203
UPC	783510285203

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

### Packaging

Carton	1
Weight Per each	58

### Uses, Certifications, and Standards

nema rating	12 Indoor, dust-resistant
-------------	---------------------------