



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A24H20BLP 24X20X8 N4 CH CLMP CVR

*Hoffman Enclosures, Inc.*

Catalog Number	A24H20BLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 4, 24X20X8, Gray, Mild Steel
Weight per unit	38.0 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

### Features

ip rating	IP66
Material	MILD STEEL

### Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

### Dimensions and Weight

Depth	8
Height	24
Size	24.00x20.00x8.00 in
Width	20

### Descriptions

Description	24X20X8 N4 CH CLMP CVR
extra long description	NVENT HOF A24H20BLP Type 4 Encl. 24
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 4, 24x20x8, Gray, Mild Steel
Product Type	Type 4 Encl. 24.00X20.00X8.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510244408
Manufacturers Part Number	A24H20BLP
UPC	783510244408

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	38

## Uses, Certifications, and Standards

Application	Controls and Drives
nema rating	12 Indoor, dust-resistant