



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A24H24BLP 24X24X8 N4 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A24H24BLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wall-Mount Enclosure, Steel, Type 4 Continuous Hinge, Wall Mount, Gray, Polyester Powder Paint, 24 In Overall Width, 24 In Overall Length, 8 In Overall Height, 43 LB
Weight per unit	43.0 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated

Dimensions and Weight

Depth	8
Height	24
Size	24.00x24.00x8.00 in
Width	24

Descriptions

Description	24X24X8 N4 CH CLMP CVR
extra long description	NVENT HOF A24H24BLP Type 4 Encl. 24
Features	These single-door enclosures feature a hinged door with clamps on three sides to create a secure seal in indoor or outdoor environments. The gray polyester powder finish inside and out provides enhanced corrosion protection in outdoor applications.

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510244507
UPC	783510244507

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

Packaging

Carton	1
Weight Per each	43

Uses, Certifications, and Standards

nema rating	12 Indoor, dust-resistant
-------------	---------------------------