



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100
65803-0000, MO Springfield
Phone: 417-429-1665
Fax: 417-429-1666



A30HS2412GQRLP 30.25X24.25X12 N4X FG Discnct HC *Hoffman Enclosures, Inc.*

Catalog Number	A30HS2412GQRLP
Manufacturer	Hoffman Enclosures, Inc.
Description	Fiberglass Disconnect Type 4X, 30.25X24.25X12.00, LT Gray, Fiberglass
Weight per unit	46.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
-----------	------

Material, Color, and Finish

Color	Gray
Color Code	RAL 7035
Finish	Smooth Matte

Dimensions and Weight

Depth	12
Height	30.25
Size	30.25x24.25x12.00 in
Width	24.25

Descriptions

Description	30.25X24.25X12 N4X FG DISCNCT HC
extra long description	NVENT HOF A30HS2412GQRLP TYPE 4X DI
Features	For effective and economical disconnect protection in the harshest corrosive environments, these enclosures provide secure door closure through the use of Type 304 stainless steel slotted quarter-turn latches. Each Fiberglass Disconnect, Type 4X is furnished with bracket affixed to door for attaching disconnect door catch (interlock) and instructions for installing disconnect handle (handle not included).
Long Description	Fiberglass Disconnect Type 4X, 30.25x24.25x12.00, Lt Gray, Fiberglass
Product Type	Type 4X Disconnect Enclosure
Short Description	TYPE 4X DISCONNECT ENCLOSURE

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510132378
Manufacturers Part Number	A30HS2412GQRLP
UPC	783510132378



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2260 N Burton Ave Suite 100
65803-0000, MO Springfield
Phone: 417-429-1665
Fax: 417-429-1666

Taxonomies, Classifications, and Categories

Type Fiberglass Wall Mounted Industrial Disconnect Enclosures

Packaging

Carton 1

Weight Per each 46

Uses, Certifications, and Standards

Application Arc Flash Safety;Controls and Drives;Corrosive Environments

nema rating 4X