



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A362412LP 36X24X12 N12 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A362412LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Continuous Hinge Enclosure With Clamps LP Type 12, 36X24X12, Gray, Mild Steel
Weight per unit	79.0 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

### Features

ip rating	IP65
Material	MILD STEEL

### Material, Color, and Finish

Finish	Powder Coated
--------	---------------

### Dimensions and Weight

Depth	12
Height	36
Size	36.00x24.00x12.00 in
Width	24

### Descriptions

Description	36X24X12 N12 CH CLMP CVR
extra long description	NVENT HOF A362412LP ENCLOSURE 36.00
Features	For applications requiring a bright white interior to increase control visibility, this enclosure includes a padlocking hasp and staple for security and screw-down clamps for secure closure.
Long Description	Continuous Hinge Enclosure with Clamps LP Type 12, 36x24x12, Gray, Mild Steel
Product Type	Enclosure 36.00X24.00X12.00

### Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510278700
Manufacturers Part Number	A362412LP
UPC	783510278700

### Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Mild Steel Wall Mounted Industrial Enclosures

### Packaging

Carton	1
Weight Per each	79



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application .....	Controls and Drives .....
nema rating .....	12 Indoor, dust-resistant .....