



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358



A36H3612SS6LP 36X36X12 N4X SS6 CH CLMP CVR

Hoffman Enclosures, Inc.

Catalog Number	A36H3612SS6LP
Manufacturer	Hoffman Enclosures, Inc.
Description	Wallmount Hinged With Nema Clamps Type 4X, 36X36X12, Brushed, SS316
Weight per unit	105.0 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

ip rating	IP66
Material	Stainless Steel;Stainless Steel 316L

Material, Color, and Finish

Color	Unpainted
Finish	Brushed #4

Dimensions and Weight

Depth	12
Height	36
Size	36.00x36.00x12.00 in
Width	36

Descriptions

Description	36X36X12 N4X SS6 CH CLMP CVR
extra long description	NVENT HOF A36H3612SS6LP Stainless E
Features	For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants.
Long Description	Wallmount Hinged with NEMA Clamps Type 4X, 36x36x12, Brushed, SS316
Product Type	Stainless Encl. 36.00X36.00X12
Short Description	Stainless Encl. 36.00x36.00x12

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510837907
Manufacturers Part Number	A36H3612SS6LP
UPC	783510837907

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Stainless Steel Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2646 SE Washington Blvd
74006-0000, OK Bartlesville
Phone: 918-876-3357
Fax: 918-876-3358

Packaging

Carton	1
Weight Per each	105

Uses, Certifications, and Standards

Application	Controls and Drives; Corrosive Environments
nema rating	4X