



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



A530M 30 Min Twist Timer Ivory

Nsi Industries

Catalog Number	A530M
Manufacturer	Nsi Industries
Description	Timer, 30 Min Time Setting Mode, SPDT Contact Form, 30 Min Time Setting, 125/250/277 V Ac, 1 Pole, Ivory, +32 °F Operating Temperature, +122 °F Operating Temperature, 3 X 5 In Size, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	30 Minute

Descriptions

Description	30 MIN TWIST TIMER IVORY
extra long description	TORK A530M 30 Minute Spring Wound T

Manufacturer Information

GTIN	00786261150141
UPC	786261150141

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Spring Wound In Wall Time Switch

Packaging

Carton	1
Package	6
Weight Per each	0.4

Uses, Certifications, and Standards

Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus