



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A560MH 60MIN Spring Wound TMR

*Nsi Industries*

Catalog Number	A560MH
Manufacturer	Nsi Industries
Description	The Tork A560MH 60-Minute Spring-Wound In-Wall Twist Timer With An Ivory Faceplate Is Designed to Control A Variety Of Indoor Appliances and Lights. Automate Your Home or Office to Save Energy and Money Using The Simple Twist Knob and Reliable Mechanical Timekeeping. Features A Hold Setting to Remain In The On Position and Fits Into A Standard Electrical Box For In-Wall Mounting. Designed For Indoor Loads Such As Lights, Whole House Fans, Air Compressors, Water Heaters or Motors.
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

### Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	60 Minute

### Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	60MIN SPRING WOUND TMR
extra long description	TORK A560MH Interval Timer 60 Min H
Features	The TORK A560MH spring-wound in-wall twist timer carries our legacy of innovation and quality with reliable timekeeping and consistent performance. Use twist timers to set a countdown for automatically shutting off appliances or lighting, saving you energy and trouble. No more forgetting to turn off a garage light or attic fan: with a twist timer, simply wind the knob to the correct duration and automate the process. TORK twist timers are at home in residential environments or a range of commercial applica
Long Description	The TORK A560MH 60-Minute Spring-Wound In-Wall Twist Timer with an ivory faceplate is designed to control a variety of indoor appliances and lights. Automate your home or office to save energy and money using the simple twist knob and reliable mechanical timekeeping. Features a hold setting to remain in the on position and fits into a standard electrical box for in-wall mounting. Designed for indoor loads such as lights, whole house fans, air compressors, water heaters or motors.
Product Type	Interval Timer 60 Min Hold White
Special Features	Ivory 60 Minute With Hold In Wall Time Switch

## Manufacturer Information

Brand	NSi
GTIN	00786261150226
Manufacturers Part Number	A560MH
UPC	786261150226

## Taxonomies, Classifications, and Categories

Category Description	TIMERS
Type	Spring Wound In Wall Time Switch

## Packaging

Carton	1
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	NSI
Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus