



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## A8824RT 8X8X24 N3R SC Wway

*Hoffman Enclosures, Inc.*

|                  |   |
|------------------|---|
| Catalog Number   | A8824RT   |
| Manufacturer     | Hoffman Enclosures, Inc.  |
| Description      | Wiring Trough, Screw Cover, Gray, Steel, 24 In Overall Length, 8 In Overall Height, 8 In Overall Width, Polyester Powder Paint, 14, 24 LB |
| Weight per unit  | 24.0 (lbs/each)   |
| Product Category | Nema Type 3R Trough & Gutter  |

### Material, Color, and Finish

|            |         |
|------------|---------|
| Color Code | ANSI 61 |
|------------|---------|

### Dimensions and Weight

|       |                    |
|-------|--------------------|
| Depth | 24                 |
| Size  | 8.00x8.00x24.00 in |
| Width | 8                  |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 8X8X24 N3R SC WWAY   |
| extra long description | NVENT HOF A8824RT Wiring Trough 8.0  |
| Features               | Screw-Cover Wiring Trough, Type 3R is used for protecting wire and cable distribution, junctions and terminations in outdoor applications that may be exposed to wet conditions. A Padlock Hasp Kit can be installed for increased security. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Nvent Hoffman  |
| GTIN  | 00783510383800 |
| UPC   | 783510383800   |

### Taxonomies, Classifications, and Categories

|                      |                               |
|----------------------|-------------------------------|
| Category Description | STEEL WIRE WAY JUNCTION BOXES |
| Type                 | Trough                        |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 24 |

### Uses, Certifications, and Standards

|             |                                   |
|-------------|-----------------------------------|
| Application | Power Distribution                |
| nema rating | 3R Weather-resistant, except dust |