



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ABMMAD 3/4X3/4" WHT CBL Tie MNT *Panduit Corporation*

Catalog Number	ABMMAD
Manufacturer	Panduit Corporation
Description	Panduit'S Abmm-A-D Rubber-Based Adhesive Back Cable Tie Mounts Have Been Designed For Fast Installation and Long-Term Performance. These Mounts Can Be Used With Miniature and Intermediate Cables Ties. Made Of Abs Plastic and Intended For Use In Indoor Environments. They Are 0.75" X 0.75" (19.1MM X 19.1MM), Supplied In Strips Of 2, Are White In Color and Come In Packages Of 500.
Weight per unit	0.0070 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Other
Material	ABS
media	Yes
Temperature Range	-20°F - 120°F (-29°C - 49°C)

### Material, Color, and Finish

Color	White
-------	-------

### Descriptions

Description	3/4X3/4" WHT CBL TIE MNT
extra long description	PAN ABMM-A-D ABMM-A-D Cable Tie Mou
Long Description	Panduit's ABMM-A-D rubber-based adhesive back cable tie mounts have been designed for fast installation and long-term performance. These mounts can be used with miniature and intermediate cables ties. Made of ABS plastic and intended for use in indoor environments. They are 0.75" x 0.75" (19.1mm x 19.1mm), supplied in strips of 2, are white in color and come in packages of 500.
Product Type	Abmm-A-D Cable Tie Mount, White, Abs, Rubber Adh., 0.75X0.75

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983585014
Manufacturers Part Number	ABMM-A-D
UPC	074983585014



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie Mount

## Packaging

Carton	500
Package	1000
Weight Per each	0.007

## Uses, Certifications, and Standards

Application	Indoor
Mounting	Adhesive Tape
Operating Temperature	120
standard	CE Compliant, UL Recognized: E136577, RoHS Compliant