



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ABMMAD 3/4X3/4" WHT CBL Tie MNT *Panduit Corporation*

Catalog Number	ABMMAD
Manufacturer	Panduit Corporation
Description	Panduit'S Abmm-A-D Rubber-Based Adhesive Back Cable Tie Mounts Have Been Designed For Fast Installation and Long-Term Performance. These Mounts Can Be Used With Miniature and Intermediate Cables Ties. Made Of Abs Plastic and Intended For Use In Indoor Environments. They Are 0.75" X 0.75" (19.1MM X 19.1MM), Supplied In Strips Of 2, Are White In Color and Come In Packages Of 500.
Weight per unit	0.0070 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Other
Material	ABS
media	Yes
Temperature Range	-20°F - 120°F (-29°C - 49°C)

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	3/4X3/4" WHT CBL TIE MNT
extra long description	PAN ABMM-A-D ABMM-A-D Cable Tie Mou
Long Description	Panduit's ABMM-A-D rubber-based adhesive back cable tie mounts have been designed for fast installation and long-term performance. These mounts can be used with miniature and intermediate cables ties. Made of ABS plastic and intended for use in indoor environments. They are 0.75" x 0.75" (19.1mm x 19.1mm), supplied in strips of 2, are white in color and come in packages of 500.
Product Type	Abmm-A-D Cable Tie Mount, White, Abs, Rubber Adh., 0.75X0.75

Manufacturer Information

Brand	PANDUIT
GTIN	00074983585014
Manufacturers Part Number	ABMM-A-D
UPC	074983585014



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie Mount

Packaging

Carton	500
Package	1000
Weight Per each	0.007

Uses, Certifications, and Standards

Application	Indoor
Mounting	Adhesive Tape
Operating Temperature	120
standard	CE Compliant, UL Recognized: E136577, RoHS Compliant