



## NATURAL CABLE TIES (4.75 IN), PACK OF 100

AC4000100 |

### FEATURES & BENEFITS

High-strength and low-profile, these 4.75-inch ties help keep wires and cables neat and orderly for superior installations. Package contains 100 cable ties.



- Secure notched locking prevents cable tie slippage
- Small form factor head reduces cable snags and eases pulling
- 50-lb tensile strength
- Convenient resealable bag
- Also available in black

### SPECIFICATIONS

Bundle Diameter: 0.118" ~ 1.06" (3mm ~ 27mm)

Hardware Type: Pawl fastener

Tensile Strength: 50 lbs (22 kg)

#### GENERAL INFO

Color: Natural

Finish: Smooth

Type: Durable nylon cable ties keeps wires and cables neat and orderly

Special Features: High-strength, low profile

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Length (Metric): 120 mm

Length (US): 4.75"

Width (Metric): 4.8 mm  
Width (US): 0.189"  
Thickness (Metric): 1.35 mm  
Thickness (US): 0.05"

#### **TECHNICAL INFORMATION**

Material: Nylon 66, Vydne® 21SPF thermoplastic  
Supported Standards: UL, RoHS

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN



## NATURAL CABLE TIES (4.75 IN), PACK OF 100

AC4000100 |

### FEATURES & BENEFITS

High-strength and low-profile, these 4.75-inch ties help keep wires and cables neat and orderly for superior installations. Package contains 100 cable ties.



- Secure notched locking prevents cable tie slippage
- Small form factor head reduces cable snags and eases pulling
- 50-lb tensile strength
- Convenient resealable bag
- Also available in black

### SPECIFICATIONS

Bundle Diameter: 0.118" ~ 1.06" (3mm ~ 27mm)

Hardware Type: Pawl fastener

Tensile Strength: 50 lbs (22 kg)

#### GENERAL INFO

Color: Natural

Finish: Smooth

Type: Durable nylon cable ties keeps wires and cables neat and orderly

Special Features: High-strength, low profile

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Length (Metric): 120 mm

Length (US): 4.75"

Width (Metric): 4.8 mm  
Width (US): 0.189"  
Thickness (Metric): 1.35 mm  
Thickness (US): 0.05"

#### **TECHNICAL INFORMATION**

Material: Nylon 66, Vydne® 21SPF thermoplastic  
Supported Standards: UL, RoHS

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: TAIWAN