



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ADR6044 60A 4W4P P&S Recpt (600VAC/250VDC)

Appleton/Oz Gedney



Catalog Number	ADR6044
Manufacturer	Appleton/Oz Gedney
Description	Pin and Sleeve Receptacle, 60 A, 600 V Ac 3 Phase @ 50 to 400 HZ 250 V DC, 4 Poles, 4 Wires, Epoxy Powder Coated Copper Free Aluminum, 1-1/4 In;1-1/2 In Hub Size, -40 °C Operating Temperature, +107 °C Operating Temperature, Pressure Wire Terminal, #6 to #2 Awg (Building);#6 to #4 Awg (Extra Flex) Wire Size, 3 LB
Weight per unit	3.0 (lbs/each)
Product Category	Pin & Sleeve Devices

### Features

amperage rating	60
connection	Pressure Wire Terminal
Number of Wires	4
Phase	3
Poles	4

### Descriptions

Description	60A 4W4P P&S RECPT (600VAC/250VDC)
extra long description	APP ADR6044 60A RECPT 4PS1 SCR/SPRG

### Manufacturer Information

Brand	Appleton
GTIN	00781381186438
UPC	781381186438

### Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Grounding Style 1 Receptacle

### Packaging

Carton	2
Package	6
Weight Per each	3

### Uses, Certifications, and Standards

Application	For ACP6044BC Metallic Clamping Ring Plug
Mounting standard	BOX CSA Certified: 065179;CSA Standard: C22.2 No. 182.1;NEMA FB11;UL 1682, UL 1686, UL 50E;UL Listed: E145916, E145917