



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AF116301114 104A 250-500V, 3P Contactor

*Industrial Connections &*

|                  |  |
|------------------|--|
| Catalog Number   | AF116301114  |
| Manufacturer     | Industrial Connections &   |
| Description      | A 3-Phase Contactor Suitable For Various Applications Such As Motor Starting, Isolation, By-Pass and Distribution Application Up to Max 690 V. Operated With Wide Control Voltage Range 250-500 V, 50/60 HZ and DC |
| Weight per unit  | 4.0 (lbs/each)   |
| Product Category | IEC Contactors   |

### Dimensions and Weight

|      |              |
|------|--------------|
| Size | 90x150x126mm |
|------|--------------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 104A 250-500V, 3P CONTACTOR  |
| extra long description | ABB AF116-30-11-14 CTR,3P,104A,250-  |
| Long Description       | A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 690 V. Operated with wide control voltage range 250-500 V, 50/60 Hz and DC |
| Product Type           | CTR, 3P, 104A, 250-500VAC/DC, 1/1  |
| Special Features       | Terminal type: Screw terminals   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | ABB            |
| GTIN                      | 00888614230187 |
| Manufacturers Part Number | AF116-30-11-14 |
| UPC                       | 888614230187   |

### Taxonomies, Classifications, and Categories

|                      |                       |
|----------------------|-----------------------|
| Category Description | IEC/FREEDOM CONTACTOR |
| Type                 | Contactors            |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 3.97 |

### Uses, Certifications, and Standards

|                       |                         |
|-----------------------|-------------------------|
| Operating Temperature | -25 to +50 Degrees C    |
| standard              | CB, CCC, CE, RINA, RoHS |