

elite

LIGHTING U.S.A.

WWW.IUSEELITE.COM

MAXILUME

ARCHITECTURAL LIGHTING

WWW.MAXILUME.COM



A 450 PAGE ELITE LIGHTING / MAXILUME PRODUCT GUIDE IS ALSO AVAILABLE. PLEASE ASK FOR IT FROM YOUR LOCAL REXEL DISTRIBUTOR.

Prices are Exclusively for **R E X E L** only!

ORDER FORMS - PLEASE FAX YOUR ORDER TO 323-888-1977 OR YOUR LOCAL SALES REP.

DESCRIPTION	QTY/ BOX	QTY/ PALLET	ELITE PART #	PRICE	SUGGESTED ORDER QTY	ORDER QTY.
6" INCANDESCENT ADJUSTABLE BRACKET HOUSINGS						
6" IC AIR SHUT HOUSING	6	240	B6IC-AT	\$4.15	240	
6" IC AIR SHUT HOUSING W/ QUICK CONNECTS	6	240	B6IC-AT-W	\$4.31	240	
6" IC AIR SHUT REMODEL HOUSING	6	276	B6RIC-AT	\$4.52	72	
6" IC 100W. AIR SHUT HOUSING	6	240	B600IC-AT	\$4.78	96	
6" IC 100W. DOUBLE WALL AIR SHUT HOUSING	6	160	B6IC-100-AT	\$8.07	48	
6" IC SHALLOW AIR SHUT HOUSING	6	240	B26IC-AT	\$5.09	36	
6" IC SHALLOW AIR SHUT REMODEL HOUSING	6	276	B26RIC-AT	\$5.95	36	
6" NON IC NEW CONSTRUCTION HOUSING	6	240	B6	\$4.15	24	
6" NON IC NEW REMODEL HOUSING	6	276	B6R	\$5.00	24	
6" INCANDESCENT TRIMS						
6" ALBALITE SHOWER TRIM	12	1200	B601WH	\$2.99	48	
6" FRESNEL SHOWER TRIM	12	1200	B605WH	\$2.99	48	
6" DROP OPAL SHOWER TRIM	12	960	B606WH	\$2.93	48	
6" R-30 OPEN TRIM	12	1200	B603WH	\$1.03	24	
6" R-30 WHITE METAL BAFFLE	48	1440	B630W/WH	\$1.03	144	
6" R-30 BLACK METAL BAFFLE	48	1440	B630P/WH	\$1.03	48	
6" R-40 WHITE METAL BAFFLE	48	1440	B640W/WH	\$1.04	48	
6" R-40 BLACK METAL BAFFLE	48	1440	B640P/WH	\$1.04	24	
6" R-30 WHITE PHENOLIC BAFFLE	12	600	B631W-WH	\$3.25	96	
6" A-19 CLEAR CONE REFLECTOR TRIM	12	600	B608CL-WH	\$7.00	48	
6" R-30 CLEAR CONE REFLECTOR TRIM	48	1440	B607CL-WH	\$6.25	48	
6" INCANDESCENT LOOSE SOCKET HOUSINGS						
6" IC AIR SHUT HOUSING W/ LOOSE SOCKET	6	240	EZ6IC-AT	\$4.15	1200	
6" IC AIR SHUT H. W/ LOOSE SOCKET & QUICK CON.	6	240	EZ6IC-AT-W	\$4.31	1200	
6" IC AIR SHUT REMODEL HOUSING W/ LOOSE SOCKET	6	276	B6RIC-AT	\$4.67	72	
6" INCANDESCENT TRIM						
6" POP-IN WHITE CONE BAFFLE/ TOP CLIPS	48	1440	AF631W-WH	\$2.26	1440	
6" POP-IN BLACK CONE BAFFLE/V TOP CLIPS	48	1440	AF631P-WH	\$2.26	1440	
6" POP-IN WHITE CONE BAFFLE/V TYPE CLIPS	48	1440	AF637W-WH	\$2.26	1440	
6" POP-IN BLACK CONE BAFFLE/V TYPE CLIPS	48	1440	AF637P-WH	\$2.26	1440	
6" R-30 OPEN TRIM V TYPE CLIPS	24	360	AF633W-WH	\$1.95	240	
6" FRESNEL SHOWER TRIM (FOR EZ HOUSING)	12	360	AF605WH	\$4.75	48	
6" ALBALITE SHOWER (FOR EZ HOUSING)	12	360	AF601WH	\$4.75	48	
6" R-30 CONE REFLECTOR /V TYPE CLIPS	12	360	AF632CL	\$7.95	48	
6" EYEBALL	12	360	B602W/WH	\$3.31	96	
6" REGRESSED EYEBALL	12	360	B609W/WH	\$7.50	24	
6" SLOPED INCANDESCENT HOUSINGS						
6" SLOPED IC AIR TIGHT HOUSING	6	240	B36IC-AT	\$11.50	36	
6" SLOPED IC AIR TIGHT REMODEL	6	240	B36RIC-AT	\$12.75	12	
6" SLOPED INCANDESCENT TRIM						
6" SLOPED WHITE BAFFLE	12	600	B391WH	\$10.50	24	
6" SLOPED BLACK BAFFLE	12	600	B391P	\$10.50	6	
6" CFL (CA TITLE 24 COMPLIANT) HOUSINGS						
6" IC AIR SHUT 13W CFL (CA TITLE 24 COMPLIANT)	6	240	B6PLIC-13-E-AT		48	
6" IC AIR SHUT 18W CFL (CA TITLE 24 COMPLIANT)	6	240	B6PLIC-18-E-AT		12	
6" IC AIR SHUT 26W CFL (CA TITLE 24 COMPLIANT)	6	240	B6PLIC-26-E-AT		96	
6" CFL (CA TITLE 24 COMPLIANT) TRIMS						
6" CFL POP-IN WHITE CONE BAFFLE/V TYPE CLIPS	12	600	B731W-WH	\$3.95	48	
6" CFL POP-IN CLEAR CONE REFLECTOR/V TYPE CLIPS	12	600	B721CL-WH	\$8.95	48	
6" CFL POP-IN WH. CONE BAFFLE W/ REFLEC. /V CLIPS	12	600	B722CL-W-WH	\$8.95	24	
6" CFL WH. CONE SHOWER TRIM W/ DOME GLASS	12	600	B725W-WH	\$9.50	24	
6" CFL WH. CONE SHOWER TRIM W/ FRESNEL GLASS	12	600	B706WH	\$7.25	24	
6" CFL WH. CONE SHOWER TRIM W/ ALBALITE GLASS	12	600	B705WH	\$7.25	24	
5" INCANDESCENT HOUSINGS						
5" IC AIR TIGHT HOUSING	6	240	B5IC-AT	\$5.95	240	
5" IC AIR TIGHT REMODEL	6	276	B5RIC-AT	\$5.95	48	
5" INCANDESCENT TRIM						
5" WHITE BAFFLE TRIM	12	600	B530W/WH	\$4.25	144	
5" BLACK BAFFLE TRIM WITH WHITE RING	12	600	B530P/WH	\$4.25	48	
5" EYEBALL	12	600	B502WH	\$7.50	36	
5" ALBALITE SHOWER TRIM	12	600	B501WH	\$8.00	24	
5" FRESNEL SHOWER TRIM	12	600	B505WH	\$8.00	24	
4" INCANDESCENT HOUSINGS						
4" AIR SHUT IC HOUSING	6	300	B4IC-AT	\$7.35	96	
4" NEW CONSTRUCTION HOUSING	6	300	B4-AT	\$6.30	36	
4" REMODEL HOUSING	6	300	B4R-AT	\$6.30	36	
4" INCANDESCENT TRIM						
4" WHITE PLASTIC BAFFLE	24	960	B401W/WH	\$4.25	72	
4" BLACK PLASTIC BAFFLE	24	960	B401P/WH	\$4.25	24	
4" CHROME REFLECTOR	24	960	B432CL/WH	\$6.55	24	
4" EYEBALL	24	960	B403WH	\$4.95	24	



Prices are Exclusively for **R E X E L** only!

ORDER FORMS - PLEASE CONTACT US FOR ADDITIONAL PRICING OR PRODUCT INFORMATION.

DESCRIPTION	QTY/ BOX	QTY/ PALLET	ELITE PART #	PRICE	SUGGESTED ORDER QTY	ORDER QTY.
4" WALL WASH BAFFLE TRIM	24	960	B406W/WH	\$7.25	24	
4" SHOWER TRIM	24	960	B462CL/WH	\$8.00	24	
4" LOW VOLTAGE HOUSINGS						
4" LV IC HOUSING	4	160	BL4IC-AT	\$24.50	72	
4" LV HOUSING	6	240	BL4-AT	\$17.50	24	
4" LV REMODEL HOUSING	6	240	BL4R-AT	\$17.50	48	
4" LOW VOLTAGE TRIMS						
4" LV WHITE BAFFLE	24	960	B1401W/WH	\$6.00	48	
4" LV BLACK BAFFLE	24	960	B1401P-WH	\$6.00	12	
4" LV CHROME REFLECTOR	24	960	B1402CL-WH	\$7.50	24	
4" LV FULLY ADJUSTABLE	24	960	B1406W/WH	\$13.95	24	
4" LV SLOT APERTURE	24	960	B1411WH	\$7.25	24	
4" LV WHITE EYE BALL	24	960	B1404W/WH	\$6.95	24	
4" LV WHITE PIN HOLE	24	960	B1414W/WH	\$6.95	24	
4" LV SEMI ADJUSTABLE	24	960	B1412W/WH	\$10.00	24	
4" LV SHOWER TRIM	24	960	B1462CL/WH	\$10.00	24	
4" LV WALL WASH	24	960	B1416W/WH	\$7.50	24	
T5-UNDER CABINET LIGHTING						
12" UNDER CABINET	6	576	EU-12	\$8.65	48	
21" UNDER CABINET	6	288	EU-21	\$13.35	24	
24" UNDER CABINET	6	288	EU-24	\$14.50	48	
33" UNDER CABINET	6	192	EU-33	\$17.00	24	
42" UNDER CABINET	6	144	EU-42	\$18.50	24	
T8-UNDER CABINET LIGHTING						
18" T8/ T12 UNDER CABINET	5	320	EZU-18-T8/T12-E	\$11.75	48	
24" T8/ T12 UNDER CABINET	5	240	EZU-24-T8/T12-E	\$12.75	48	
36" T8/ T12 UNDER CABINET	5	160	EZU-36-T8/T12-E	\$17.50	24	
48" T8/ T12 UNDER CABINET	5	120	EZU-48-T8/T12-E	\$18.25	24	
PUCK LIGHTS						
WHITE 3 LIGHT PUCK LIGHT KIT	12		HU-03-3-WH	\$22.00	6	
BLACK 3 LIGHT PUCK LIGHT KIT	12		HU-03-3-BK	\$22.00	3	
CHROME 3 LIGHT PUCK LIGHT KIT	12		HU-03-3-CH	\$25.00	3	
GOLD 3 LIGHT PUCK LIGHT KIT	12		HU-03-3-PB	\$25.00	3	
WHITE 120 V. PUCK LIGHT	12		HU-10WH	\$8.25	12	
BLACK 120 V. PUCK LIGHT	12		HU-10BK	\$8.25	6	
GOLD 120 V. PUCK LIGHT	12		HU-10PB	\$9.25	6	
CHROME 120 V. PUCK LIGHT	12		HU-10CH	\$9.25	6	
LOW VOLTAGE TRANSFORMERS						
75 W. L.V. TRANSFORMER	24		ELV-75	\$9.50	6	
105 W. L.V. TRANSFORMER	24		ELV-105	\$16.50	6	
150 W. L.V. TRANSFORMER	24		ELV-150	\$19.50	6	
1 CIRCUIT TRACK						
4FT TRACK WHITE	12		ET-4-WH	\$9.25	6	
8FT TRACK WHITE	12		ET-8-WH	\$17.25	6	
4FT TRACK BLACK	12		ET-4-BK	\$9.25	3	
8FT TRACK BLACK	12		ET-8-BK	\$17.25	3	
LOW VOLTAGE TRACK HEAD						
50W WHITE GIMBAL RING	24		ET-401-WH	\$15.00	6	
50W BLACK GIMBAL RING	24		ET-401-BK	\$15.00	3	
50W BLACK CYLINDER TRACK FIXTURE	24		ET-402-BK	\$18.00	6	
50W WHITE CYLINDER TRACK FIXTURE	24		ET-402-WH	\$18.00	6	
50W BLACK SOFT SQUARE TRACK FIXTURE	24		ET-403-BK	\$18.00	6	
50W WHITE SOFT SQUARE TRACK FIXTURE	24		ET-403-WH	\$18.00	6	
LINE VOLTAGE TRACK HEADS						
WHITE GIMBAL RING 50W PAR20	12		ET-212-WH	\$7.25	12	
75W PAR30 WHITE GIMBAL RING	12		ET-213-WH	\$7.25	12	
BLACK GIMBAL RING 50W PAR20	12		ET-212-BK	\$7.25	6	
75W PAR30 BLACK GIMBAL RING	12		ET-213-BK	\$7.25	6	
ACCESSORIES - 1 CIRCUIT TRACK						
LIVE END TRACK CONNECTOR WHITE	24		ET-101-WH	\$2.75	6	
LIVE END TRACK CONNECTOR BLACK	24		ET-101-BK	\$2.75	3	
FLOATING CANOPY WHITE	24		ET-103-WH	\$4.80	6	
FLOATING CANOPY BLACK	24		ET-103-BK	\$4.80	3	
MINI COUPLING WHITE	24		ET-107-WH	\$2.50	6	
MINI COUPLING BLACK	24		ET-107-BK	\$2.50	3	
L CONNECTOR W/ POWER ENTRY WHITE	24		ET-108-WH	\$4.00	6	
L CONNECTOR W/ POWER ENTRY BLACK	24		ET-108-BK	\$4.00	3	
ROPE LIGHT						
120 V. INSTANT FLEXILIGHT CLEAR	1		ER1-150-CL	\$99.00	2	
120 V. INSTANT LED FLEXILIGHT CLEAR	1		ER-LED-12-150-CW	\$775.00	1	