



SKU: AGC-1

UPC: 0783669000603

Features & Benefits:

Description: Permground Aluminum Ground Clamp, Dual Rated, Conductor Range 1/0-14, Pipe Sizes 1/2 to 1in, Rebar Sizes #4-#6, UL

Specs

Additional Class Attributes

Connection	Mechanical
Number of Conductors	1
Number of Ports / Wireways	1
Wire Orientation	Parallel

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	1/0 Str - 14 Str
Conductor Range CU Solid (Primary, run, main, line)	10 Sol - 14 Sol
Conductor Range CU Stranded (Primary, run, main, line)	1/0 Str - 14 Str
Conductor Range AL Solid (Primary, run, main, line)	10 Sol - 14 Sol
NPS/IPS Pipe Size	3/4
Rebar Size(s) Main	#5 (5/8)

Dimensions

Drive Size Main	NA
Drive Type Main	Slotted
Height (IN)	1.611
Height BX (IN)	2.75
Height (mm)	40.9194
Length (IN)	2.25
Weight (LB)	0.05
Weight BX (LB)	3.955
Width (IN)	0.688
Width BX (IN)	6
Width (mm)	17.4752

Material and Finish

Clamping Hardware Finish	Zinc Clear Trivalent Chromate
Clamping Hardware Material	Steel
Conductor Material	Copper
Connector Finish	Tin
Material	Aluminum
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 25
Direct Burial	No
Dual Rated	Yes
NEMA Code	S-573-2
UPC Code	78366900060

Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	667P
UL / CULUS Specification	UL 467 Listed
UL File Number	E34440

Bolt and Screw Sizes

Clamping Bolt Size	1/4-20
Wire Binding Torque	2/0 - 2 AWG = 50