



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## AGC20 20A 32V 1/4X1-1/4 Rohs Fa Glass Fuse *Bussmann Fuses*

Catalog Number	AGC20
Manufacturer	Bussmann Fuses
Description	Buss Agc-20 Agc Glass Fuse - 1/4 X
Weight per unit	0.0060 (lbs/each)
Product Category	Tools & Testers

### Features

amperage rating	20 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	32 VAC

### Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

### Descriptions

Description	20A 32V 1/4X1-1/4 ROHS FA GLASS FUSE
Long Description	BUSS AGC-20 AGC GLASS FUSE - 1/4 x
Product Type	Agc Glass Fuse - 1/4 X 1-1/4 - 20 Amp
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap

### Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712703949
Manufacturers Part Number	AGC-20
UPC	051712703949

### Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Fast Acting

### Availability

Manufacturer Status	Inactive
Status	Inactive

### Packaging

Carton	5
Weight Per each	0.006



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application  
standard

Electronic Circuits  
UL 248-14, CSA