



SKU: AGC-4

UPC: 0783669000641

Features & Benefits:

Description: Permagraund Aluminum Ground Clamp, Conductor Range 250-6, Pipe Sizes 2-1/2 to 4in, UL

Specs

Additional Class Attributes

Connection	Mechanical
Number of Conductors	1
Number of Ports / Wireways	1
Wire Orientation	Parallel

Conductor Ranges

Conductor Range AL Stranded (Primary, run, main, line)	250 kcmil - 6 Str
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Stranded (Primary, run, main, line)	250 kcmil - 6 Str
Conductor Range AL Solid (Primary, run, main, line)	NA
NPS/IPS Pipe Size	2-1/2

Dimensions

Drive Size Main	5/16
Drive Type Main	Internal Hex
Height (IN)	4.063
Height BX (IN)	4.25
Height (mm)	103.2002
Length (IN)	6.312
Length (mm)	160.3248
Weight (LB)	0.276
Weight BX (LB)	3.7109
Width (IN)	1
Width BX (IN)	7.75
Width (mm)	25.4

Material and Finish

Clamping Hardware Finish	Zinc Clear Trivalent Chromate
Clamping Hardware Material	Steel
Conductor Material	Aluminum
Connector Finish	Tin
Material	Aluminum
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 4
Direct Burial	No
Dual Rated	Yes
NEMA Code	S-573-2
UPC Code	78366900064

Testing Standards

Prop65 Compliance	This product is in compliance with Prop65. It is not known to contain any chemicals associated with this regulation
UL Control Number	667P
UL / CULUS Specification	UL 467 Listed
UL File Number	E34440

Bolt and Screw Sizes

Clamping Bolt Size	3/8-16
Wire Binding Torque	275