



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGFTR2152W4 TR Gfci 15A WH

Pass & Seymour/Legrand

Catalog Number	AGFTR2152W4
Manufacturer	Pass & Seymour/Legrand
Description	Tamper-Resistant Gfci, 15A White
Weight per unit	0.2925 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Side & Back Wire
Connection Type	Internal Pressure Plates
indoor/outdoor	Indoor
interrupt rating	.025 Second Nominal
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Self-Test, GFCI, Tamper-Resistant
Phase	Single
Poles	2
trip range	4 to 6 mA
Voltage Rating	125

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Height	2.66
Length	1.82
Width	1.77

Descriptions

Description	TR GFCI 15A WH
extra long description	ADO AGFTR2152W4 TAMPER-RESISTANT GF
Long Description	TAMPER-RESISTANT GFCI, 15A WHITE
Product Type	Tamper-Resistant Gfci, 15A WH
Special Features	GFCIs protect against serious injury due to electric shock. They are required by National Electrical Code in kitchens and bathrooms



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	legrand
GTIN	00785007052626
Manufacturers Part Number	AGFTR2152-W4
UPC	785007052626

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Tamper-Resistant GFCI Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	4
Weight Per each	0.2925

Uses, Certifications, and Standards

Application	Residential Outlet
environmental conditions	95% (relative humidity, non-condensing)
Frequency Rating	60Hz
nema rating	15A, GFCI
standard	cULus