



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGFTR2152W4 TR Gfci 15A WH

Pass & Seymour/Legrand

| | |
|------------------|----------------------------------|
| Catalog Number | AGFTR2152W4 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Tamper-Resistant Gfci, 15A White |
| Weight per unit | 0.2925 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------------|-----------------------------------|
| amperage rating | 15 |
| connection | Side & Back Wire |
| Connection Type | Internal Pressure Plates |
| indoor/outdoor | Indoor |
| interrupt rating | .025 Second Nominal |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| Outlet Type | Self-Test, GFCI, Tamper-Resistant |
| Phase | Single |
| Poles | 2 |
| trip range | 4 to 6 mA |
| Voltage Rating | 125 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 2.66 |
| Length | 1.82 |
| Width | 1.77 |

Descriptions

| | |
|------------------------|---|
| Description | TR GFCI 15A WH |
| extra long description | ADO AGFTR2152W4 TAMPER-RESISTANT GF |
| Long Description | TAMPER-RESISTANT GFCI, 15A WHITE |
| Product Type | Tamper-Resistant Gfci, 15A WH |
| Special Features | GFCIs protect against serious injury due to electric shock. They are required by National Electrical Code in kitchens and bathrooms |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | legrand |
| GTIN | 00785007052626 |
| Manufacturers Part Number | AGFTR2152-W4 |
| UPC | 785007052626 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | Residential Switches |
| Type | Tamper-Resistant GFCI Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 0.2925 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Residential Outlet |
| environmental conditions | 95% (relative humidity, non-condensing) |
| Frequency Rating | 60Hz |
| nema rating | 15A, GFCI |
| standard | cULus |