



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AGX2 2A 250V Small Dim Fuse

Bussmann Fuses

Catalog Number	AGX2
Manufacturer	Bussmann Fuses
Description	Eaton Agx Series Fast-Acting Fuse 2A, 250 Vac, 32 VDC
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	2 A
connection	Ferrule End X Ferrule End
dimensions	X X 1.0236 IN
interrupt rating	10 kAIC at 125 Vac100 AIC at 250 Vac
Material	Glass tubeNickel-plated brass end cap construction
Response Time	4 hr at 110%, 60 min at 135%, 5 sec at 200%
Voltage Rating	250 Vac, 32 Vdc

Dimensions and Weight

Size	0.25 In Diameter X 1.00 In Length
------	-----------------------------------

Descriptions

Description	2A 250V SMALL DIM FUSE
extra long description	EFSE AGX-2 AGX GLASS FUSE - 1/4" x
Features	Fast-acting, glass tube 1/4" x 1" ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block or fuse clip. Eaton's AGX fast-acting, glass tube 1/4" x 1" ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip.
Long Description	Eaton AGX Series Fast-acting fuse 2A, 250 Vac, 32 Vdc
Product Type	Agx Glass Fuse - 1/4" X 1" - 2 Amp
Special Features	Glass tube

Manufacturer Information

Brand	Eaton Bussmann series
GTIN	00051712704762
Manufacturers Part Number	AGX-2
UPC	051712704762

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	Not Applicable