

1/4" Dia. x 5/8" to 1" Length Ferrule Fuses

AGA-V (axial leads)

AGA

Specifications
Description: Fast-acting fuse.

Dimensions:
1/4" x 5/8"
(6.4 x 15.9mm).

Construction:
Glass tube.

Ratings:

- Volts — 125Vac (or less)
- Amps — 1-30A
- IR — 10kA (1-1 1/2A @ 125Vac)
- 200A (2-5A @ 125Vac)
- 1000A (6-30A @ 32Vac)

Agency Information: CE, Std. 248-14, UL File E19180, UL Listed, Guide JDYX 0-1 1/2A UL Recognized, Guide JDYX2 2-12A.

Features and Benefits

- Fast-acting for maximum protection.
- Size rejects insertion of other fuse types.

Typical Applications

- Electronic Circuits

Catalog Numbers (Amps)

With Axial Leads*

AGA-V-1	AGA-V-5	AGA-V-15
AGA-V-1-1/2	AGA-V-6	AGA-V-20
AGA-V-2	AGA-V-7	AGA-V-25
AGA-V-2-1/2	AGA-V-7-1/2	AGA-V-30
AGA-V-3	AGA-V-10	

Without Axial Leads

AGA-1	AGA-5	AGA-15
AGA-1-1/2	AGA-6	AGA-20
AGA-2	AGA-7	AGA-25
AGA-2-1/2	AGA-7-1/2	AGA-30
AGA-3	AGA-10	

*AGA-V is UL Listed 0-5A, UL Recognized 6-12A.



AGW

Specifications
Description: Fast-acting fuse.

Dimensions: 1/4" x 7/8"
(6.4 x 22.2mm).

Construction: Glass tube.

Ratings:

- Volts — 32Vac
- Amps — 1-30A

Features and Benefits

- Fast-acting for maximum protection.

Typical Applications

- Electronic Circuits

Catalog Numbers (Amps)

AGW-1	AGW-4	AGW-15
AGW-1-1/2	AGW-5	AGW-20
AGW-2	AGW-6	AGW-25
AGW-2-1/2	AGW-7-1/2	AGW-30
AGW-3	AGW-10	



AGX

Specifications
Description: Fast-acting fuse.

Dimensions: 1/4" x 1"
(6.4 x 25.4mm).

Construction: Glass tube.

Ratings:

- Volts — 250Vac (1/200-2A)
- 125Vac (2 1/2-7A)
- 32V (8-30A)

Amps — 1/4-30A

IR — 35A (1/4-1/2A @ 250Vac)

— 100A (3/4-2A @ 250Vac)

— 10kA (1/4-5A @ 125Vac)

— 1000A (5-6A @ 125Vac)

— 1000A (8-30A @ 32Vac)

Agency Information: CE, Std. 248-14, UL File E19180 UL Listed, Guide JDYX, 0-5A UL Recognized, Guide JDYX2, 6-20A CSA File 53787; Class 1422-01.

Features and Benefits

- Size rejects insertion of other fuse types.

Typical Applications

- Electronic Circuits

Catalog Numbers (Amps)

AGX-1/4	AGX-1-1/2	AGX-8
AGX-3/16	AGX-2	AGX-10
AGX-3/8	AGX-2-1/2	AGX-15
AGX-1/2	AGX-3	AGX-20
AGX-3/4	AGX-4	AGX-25
AGX-1	AGX-5	AGX-30
AGX-1-1/4	AGX-6	
	AGX-7	

