

Eaton AH1995W

Catalog Number: AH1995W

Eaton Arrow Hart industrial grade toggle switch, Momentary toggle, #14-10 AWG, 20A, Flush, 120/277V, Side wire, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, 1-pole, 1-pole, Brass

General specifications



| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton Arrow Hart industrial grade toggle switch | AH1995W |
| | UPC |
| | 040893643250 |

| | |
|----------------------|----------------|
| Product Length/Depth | Product Height |
| 1.31 in | 3.28 in |

| | |
|---------------|----------------|
| Product Width | Product Weight |
| 1 in | 0.2 lb |

Certifications

cURus

Product specifications

Special features

Momentary toggle

Connector type

Screw

Switch type

Single-pole

Load type

MLV

FLR

LED

ELV

INC

Fan

CFL

HAL

Motor Control

Color

White

Wiring method

Side wire

Mounting method

Flush

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Number Of Poles

Single-pole

Type

Toggle switch

Voltage rating

120/277 V

Terminal enclosure material

Brass

Application

Industrial

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Multimedia

[Arrow Hart - Connecting Safety to Reliability since 1890](#)

Specifications and datasheets

[Eaton Specification Sheet - AH1995W](#)

Torque rating

14 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)