



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AH460R5W Recp Pin&Sleeve 60A 600V 3PH 3P4W WT BK *Eaton Wiring Devices*

Catalog Number	AH460R5W
Manufacturer	Eaton Wiring Devices
Description	Receptacle, 60 A, 3 Poles, 4 Wires, Plug Connection, 6.5 In Length, 5 In Width, 5.125 In Height, Thermoplastic, Blue/Gray, 0.0993 LB
Weight per unit	32.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	60
connection	Pin & Sleeve
dimensions	6.5000 IN X 5.0000 IN X 5.1250 IN
insulation	Nylon PA6-GF30FR (17)
media	Yes
Phase	3
Poles	3

Dimensions and Weight

Size	6.5 x 5 x 5.125
------	-----------------

Descriptions

Description	RECP PIN&SLEEVE 60A 600V 3PH 3P4W WT BK
extra long description	CRS-H AH460R5W RECP PIN AND SLEEVE
Features	Eaton's Arrow Hart full line of pin and sleeve devices offer sturdy nylon construction, rugged design with corrosion resistant components for lasting electrical performance, and watertight sealing that provides IP69K protection so you can feel confident in even the most severe washdown environments.

Manufacturer Information

Brand	Eaton
GTIN	00326647320890
UPC	032664732089

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	RECEPTACLE

Packaging

Carton	1
Package	16
Weight Per each	32



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

environmental conditions	IP67 & IP69k
Mounting	Flange Mount
standard	IEC, UL, CSA
Temperature Rating	Max. 30°C (86°F) after 50 cycles of overload @150% of rated current