

# Eaton AH7810UD

Catalog Number: AH7810UD

Eaton manual motor controller, Switch only, #14-10 AWG, 30A, Industrial, Panel, 600V, Front wired screw and clamp, Maintained contact, Black, Open, Three-pole, Two-position, Three-phase, Toggle switch, Copper-alloy terminal, Single-throw

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton manual motor controller	AH7810UD
<b>UPC</b>	<b>Product Length/Depth</b>
040893006048	3.75 in
<b>Product Height</b>	<b>Product Width</b>
2.38 in	2.38 in
<b>Product Weight</b>	<b>Compliances</b>
0.65 lb	NAFTA RoHS Compliant
<b>Certifications</b>	
cULus Listed	

## Product specifications

### Special features

Switch only

### Number of positions

2

### Switch type

Toggle switch

### Phase

Three-phase

### Termination style

Front screw and clamp

### Closure type

Maintained

### Color

Black

### Wiring method

Front wired screw and clamp

### Material

Glass-filled nylon

### Enclosure

Open

### Mounting method

Panel

### Allowable wire size

#14-10 AWG

### Amperage Rating

30A

### Number Of Poles

Three-pole

### Contact type

Maintained

### Type

Manual motor controller

### Device grade

Industrial

## Resources

### Catalogs

[Arrow Hart Buyers Guide Section E](#)

### Specifications and datasheets

[Eaton Specification Sheet - AH7810UD](#)

Throw

Single-throw

Operating temperature

-20 to 65 °C

Terminals

Copper-alloy, brass screw

Voltage rating

600 V

Application

Industrial



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)