ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



AHCL630P CCL PLUG 30A 250V 2P3W BL&BK

EATON WIRING DEVICES

Catalog Number	AHCL630P
Manufacturer	EATON WIRING DEVICES
Description	Eaton Arrow Hart Color Coded Locking Plug, Locking Plug, #14-8 AWG, 30A, Industrial, 250V, Back, Blue, Black, Ultra grip, Nylon, L6-30, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm)
Weight per unit	0.4200 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

Dimensions	2.2300 IN X 2.1000 IN X 2.6900 IN
Media	Yes

Descriptions

Description	CCL PLUG 30A 250V 2P3W BL&BK
Features	Eaton's Arrow Hart color coded locking devices are an industry-first solution that adds six voltage rating color codes consistent with IEC 60309 standards to locking plugs, connectors, inlets, outlets and receptacles to provide you a quick, clear and easy way to identify your circuit voltage. Available in standard NEMA configurations for 20A and 30A applications, the devices ensure long-lasting, dependable service in the most demanding environments, are built with a contemporary flare and ergonomic design
Long Description	Eaton Arrow Hart Color Coded Locking Plug, Locking Plug, #14-8 AWG, 30A, Industrial, 250V, Back, Blue, Black, Ultra grip, Nylon, L6-30, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm)
Product Type	CCL Plug 30A 250V 2P3W-BL&BK
Special Features	Industrial grd plugs & conns
Extra Long Description	EWD AHCL630P CCL Plug 30A 250V 2P3W

Manufacturer Information

Brand	Eaton
	Eaton Wiring Devices
GTIN	00032664755545
Manufacturers Part Number	AHCL630P
UPC	781430

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	Color Coded Locking

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	1
Package	40
Weight Per Each	0.4200 (lbs/each)

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility - Other
Standard	NOM,cULus Listed,RoHS Compliant,NAFTA

Specifications

Eaton AHCL630P



Catalog Number: AHCL630P

Eaton Arrow Hart Color Coded Locking Plug, Locking Plug, #14-8 AWG, 30A, Industrial, 250V, Back, Blue, Black, Ultra grip, Nylon, L6-30, Two-pole, Three-wire, Nylon, 0.38 - 1.00" (9.5 - 25.4mm)

General specifications

Product Name	**Catalog Number**
Eaton Arrow Hart Color Coded Locking Plug	AHCL630P
	UPC
	032664755545
Product Length/Depth	**Product Height**
2.23 in	2.69 in
Product Width	**Product Weight**
2.1 in	0.4 lb
Compliances	**Certifications**
RoHS Compliant	cULus Listed
NAFTA	NOM

Powering Business Worldwide

Product specifications

Special features
Voltage Color Coding

Type
Locking Plug

Amperage Rating
30A

Voltage rating
250 V

Application
Industrial

Wiring method
Back

Number of wires
3

Number Of Poles
Two-pole

Color
Blue
Black

Cord diameter
0.38-1 in (9.5-25.4 mm)

Material
Nylon

Operating temperature
-40 to 60 °C (-40 to 140 °F)

Allowable wire size
#14-8 AWG

NEMA configuration
L6-30

Torque rating
14-16 lbf-inch

Design type
Ultra grip

Face/body material
Nylon

Resources

Multimedia
Eaton Arrow Hart color coded locking devices

Specifications and datasheets
Eaton Specification Sheet - AHCL630P

Arrow Hart color coded industrial grade L6-30 locking devices spec sheet

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia