



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



AHL1030R Recp Single 30A 125/250V 3P3W H/L BK *Eaton Wiring Devices*

| | |
|------------------|--|
| Catalog Number | AHL1030R |
| Manufacturer | Eaton Wiring Devices |
| Description | Eaton Locking Receptacle, #14-8 Awg, 30A, Industrial, 125/250V, Back and Side Wiring, Black, Brass, Single, L10-30, Three-Pole, Three-Wire, Glass-Filled Nylon |
| Weight per unit | 0.3000 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|------------|-----------------------------------|
| dimensions | 1.8000 IN X 1.9600 IN X 4.5500 IN |
| media | Yes |

Descriptions

| | |
|------------------------|--|
| Description | RECP SINGLE 30A 125/250V 3P3W H/L BK |
| extra long description | EWD AHL1030R-OBS RECP SINGLE 30A 12 |
| Features | Industrial grade locking devices are designed for quick and easy installation and provide reliable performance in tough industrial environments. |
| Long Description | Eaton locking receptacle, #14-8 AWG, 30A, Industrial, 125/250V, Back and side wiring, Black, Brass, Single, L10-30, Three-pole, Three-wire, Glass-filled nylon |
| Product Type | Recp Single 30A 125/250V 3P3W H/L BK |

Manufacturer Information

| | |
|---------------------------|----------------------|
| Brand | Eaton Wiring Devices |
| GTIN | 00040893677323 |
| Manufacturers Part Number | AHL1030R-OBS |
| UPC | 040893677323 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Locking Receptacle |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.3 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Ind Facilities & Factories - Facility - Other |
| standard | UL,RoHS Compliant |