

Eaton AHMC260L

Catalog Number: AHMC260L

Eaton manual motor controller, Switch only, #14-4 AWG, 60A, Industrial, Panel, 600V, Side wired box lug, Maintained contact, Black, Open, Two-pole, Single-phase, Toggle switch, Copper-alloy terminal, Single-throw, Glass-filled nylon



General specifications

Product Name	Catalog Number
Eaton manual motor controller	AHMC260L
UPC	Product Length/Depth
040893653846	2.29 in
Product Height	Product Width
4.33 in	2.34 in
Product Weight	Compliances
0.45 lb	RoHS Compliant NAFTA
Certifications	
cULus Listed	

Product specifications

Special features

Switch only

Number of positions

2

Switch type

Toggle switch

Phase

Single-phase

Termination style

Side wired box lug

Closure type

Maintained

Color

Black

Wiring method

Side wired box lug

Material

Glass-filled nylon

Enclosure

Open

Mounting method

Panel

Allowable wire size

#14-4 AWG

Amperage Rating

60A

Number Of Poles

Two-pole

Contact type

Maintained

Type

Manual motor controller

Device grade

Industrial

Resources

Catalogs

[Arrow Hart Buyers Guide Section E](#)

Specifications and datasheets

[Eaton Specification Sheet - AHMC260L](#)

Throw

Single-throw

Terminals

Copper-alloy, brass screw

Voltage rating

600 V

Application

Industrial



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)