

BURNDY Catalog Number
UPC Number
Description
Status

AMS0
7818102410111
1/0-14 DUAL RATED SPLICE
Active

Web Use
BURNDY Product Line

Width (in)
Length (in)
Hex Size
H1

Dimensional
0.75
1.91
Slot
0.75

Number of Screws

General

2
Aluminum Mechanical Splice, 1/0-14 AWG, 7/16" Screw Dia, 2 Screws, Al/Cu Rated, Tin Plated

Product Description

Conductor(s)

Aluminum Size (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

12 AWG-1/0 AWG
12 AWG-1/0 AWG
14 AWG-1/0

Installation Torque
Type of Plating
Connector Type
Plated (Yes or No)
Product Material

Physical

50
Tin
Splice, Reducer
Y
Aluminum

Rated for Direct Burial
UL Listed
CSA Certified
ROHS Compatible
Industry Standards

Approvals / Certifications

N
Y
Y
Exempt
UL467

Documentation

For further technical assistance, please contact us


BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175



BURNDY Catalog Number
UPC Number
Description
Status

AMS0
7818102410111
1/0-14 DUAL RATED SPLICE
Active

Web Use
BURNDY Product Line

Width (in)
Length (in)
Hex Size
H1

Dimensional
0.75
1.91
Slot
0.75

Number of Screws

General

2
Aluminum Mechanical Splice, 1/0-14 AWG, 7/16" Screw Dia, 2 Screws, Al/Cu Rated, Tin Plated

Product Description

Conductor(s)

Aluminum Size (Range)
Copper Solid Size (Range)
Copper Stranded (Range)

12 AWG-1/0 AWG
12 AWG-1/0 AWG
14 AWG-1/0

Installation Torque
Type of Plating
Connector Type
Plated (Yes or No)
Product Material

Physical

50
Tin
Splice, Reducer
Y
Aluminum

Rated for Direct Burial
UL Listed
CSA Certified
ROHS Compatible
Industry Standards

Approvals / Certifications

N
Y
Y
Exempt
UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175