

Eaton AN16BN0AC

Catalog Number: AN16BN0AC

Eaton Freedom NEMA motor control starter, Non-Reversing Reset Overload Relay Starter, 1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V maximum horsepower, 120V/60 Hz or 110V/50 Hz coil voltage, 18A, Three-pole, Size 0



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN16BN0AC
	UPC
	782113971568
Product Length/Depth	Product Height
4.61 in	3.31 in
Product Width	Product Weight
4.38 in	2.6 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified
	Catalog Notes
	Heater Packs must be purchased separately

Special features

Starter w/C306 bi-metal OLR

HP rating - max

1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V

Phase

Single-phase, three-phase

Amperage Rating

18A

Size

0

Mounting

Horizontal

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[AN16BN0_C 2D Drawing Xchange](#)

[AN16BN0_C 3D Model Xchange](#)

[AN16BN0_C 3D Inventor](#)

[AN16BN0_C AutoCAD 2D Footprint \(mm\)](#)

[AN16BN0_C AutoCAD 2D Footprint](#)

[AN16BN0_C 2D PDF](#)

Specifications and datasheets

[Quick Selector - NEMA Contactors](#)

[Eaton Specification Sheet - AN16BN0AC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)