

Eaton AN16BN0CC

Catalog Number: AN16BN0CC

Eaton Freedom NEMA motor control starter, Non-Reversing Reset Overload Relay Starter, 1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V maximum horsepower, 480V/60 Hz or 440V/50 Hz coil voltage, 18A, Three-pole, Size 0



General specifications

Product Name	Catalog Number
Eaton Freedom NEMA motor control starter	AN16BN0CC
	UPC
	782113971582

Product Length/Depth	Product Height
6 in	3.4 in

Product Width	Product Weight
1.9 in	2 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Catalog Notes

Heater Packs must be purchased separately

defaultTaxonomyAttributeLabel

Special features

Starter w/C306 bi-metal OLR

HP rating - max

1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V

Phase

Single-phase, three-phase

Number of Poles

Three-pole

Amperage Rating

18A

Size

0

Mounting

Horizontal

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[AN16BN0_C 3D Model Xchange](#)

[AN16BN0_C 2D PDF](#)

[AN16BN0_C 3D Inventor](#)

[AN16BN0_C AutoCAD 2D Footprint \(mm\)](#)

[AN16BN0_C AutoCAD 2D Footprint](#)

[AN16BN0_C 2D Drawing Xchange](#)

Specifications and datasheets

[Eaton Specification Sheet - AN16BN0CC](#)

[Quick Selector - NEMA Contactors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)